

ESE Air Terminal Remote Tester Kit



nVent ERICO Early Streamer Emission (ESE) Air Terminal Remote Testing System provides complete autonomous monitoring of your ESE system. This kit includes both the nVent ERICO ESE Terminal for Remote Tester and the nVent ERICO ESE Air Terminal Remote Tester, which can quickly and easily be assembled on-site by hand. The fully autonomous monitoring system for early streamer emission air terminals (ESEAT), requires no additional costly hardware, software, monitoring or interface systems. Save time and money by avoiding equipment rentals required to manually test your ESE system. The nVent ERICO ESE Air Terminal Remote Tester features three LED lights to alert you if your ESEAT, tester, or complete system becomes inoperable at any time throughout the day. For easy monitoring, the LED lights are color-coded to indicate which part of the system needs replacement. The remote feature of the nVent ERICO ESE Air Terminal Remote Tester allows users to quickly ensure their lighting protection system is fully operational and their facility is protected at any time.

FUNKTIONER

Allows for uninterrupted, daily monitoring of ESE system status

Fully autonomous

Requires no additional software or accessories

Colored LED lights indicate part-specific malfunctions to allow for quick and easy replacement

Easy installation and fast start-up time

Solar powered for sustainability (no batteries required)

Superior corrosion resistance, even in high salinity environments

Suitable for use with a variety of downconductor systems including tape and stranded conductors in addition to insulated downconductors such as nVent ERICO ISO_NV and nVent ERICO Ericore conductors

LED lights are visible up to 100 meters away

SPECIFIKATIONER

Table 1/2

Katalognummer	Materiale	Triggered Advance, ΔT	Complies With	Enclosure Rating	Impulse Current (Iimp)	Status Indication
---------------	-----------	-------------------------------	---------------	------------------	------------------------	-------------------

SI60I316RT-KIT	Stainless Steel 316L (EN 1.4404)	60µs	NF C17- 102:2011, NP 4426:2013, UNE 21186:2011, NF EN 62561-6 clause 6.6.4	IP 68	100kA 10/350 µs	LED
----------------	--	------	---	-------	--------------------	-----

Table 2/2

Katalognummer	Working Temperature
SI60I316RT-KIT	-20 to 60 °C

ADVARSEL

nVent-produkter skal kun installeres og anvendes som angivet i nVents produktvejledninger og træningsmaterialer. Vejledninger er tilgængelige på www.nvent.com og hos din nVent kundeservicerepræsentant. Forkert installation, misbrug, fejlanvendelse eller anden undladelse af fuldt ud at følge nVents instruktioner og advarsler kan medføre funktionsfejl, materielle skader, alvorlige personskader eller død og/eller ugyldiggøre din garanti.

North America

+1.800.753.9221
Option 1 – Customer Care
Option 2 – Technical
Support

Europe

Netherlands:
+31 800-0200135
France:
+33 800 901 793

Europe

Germany:
800 1890272
Other Countries:
+31 13 5835404

APAC

Shanghai:
+ 86 21 2412 1618/19
Sydney:
+61 2 9751 8500



Vores kraftfulde portefølje af mærker:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE