

Disconnectable PEN System



CERTIFICERINGER



FUNKTIONER

Dedicated product allowing separation from PEN to PE+N

Unique solution for TN-C/TN-S networks

Safe disconnectable system

Clear identification

Prevents measurement errors

Avoid reconnection errors

Screen stickers included in 12 languages

SPECIFIKATIONER

Complies With: IEC® 60439.1; IEC® 61439.1

Table 1/2


Katalognummer	Artikelnummer	Max Current Rating, IEC	Thread Size (TS)	Busbar Width	Busbar Thickness	Dybde (D)
PEN-D100	568805	250A	M8	20 mm	5 mm	68.2mm

Katalognummer	Artikelnummer	Max Current Rating, IEC	Thread Size (TS)	Busbar Width	Busbar Thickness	Dybde (D)
PEN-D75	568800	125A	M6	15 mm	5 mm	68.2mm
PEN-D300	568810	630A	M10	30 mm	10 mm	78.2mm

Table 2/2

Katalognummer	Artikelnummer	Height (H)	Width (W)	A	B
PEN-D100	568805	170 mm	128 mm	100 mm	112.5 mm
PEN-D75	568800	120 mm	96 mm	100 mm	75 mm
PEN-D300	568810	170 mm	128 mm	100 mm	112.5 mm

DIAGRAMS



ADVARSEL

nVent-produkter skal kun installeres og anvendes som angivet i nVents produktvejledninger og træningsmaterialer. Vejledninger er tilgængelige på www.nvent.com og hos din nVent kundeservicerepræsentant. Forkert installation, misbrug, fejlanvendelse eller anden undladelse af fuldt ud at følge nVents instruktioner og advarsler kan medføre funktionsfejl, materielle skader, alvorlige personskader eller død og/eller ugyldiggøre din garanti.

North America

+1.800.753.9221

Option 1 – Customer Care

Option 2 – Technical

Support

Europe

Netherlands:

+31 800-0200135

France:

+33 800 901 793

Europe

Germany:

800 1890272

Other Countries:

+31 13 5835404

APAC

Shanghai:

+ 86 21 2412 1618/19

Sydney:

+61 2 9751 8500



Vores kraftfulde portefølje af mærker:

CADDY

ERICO

HOFFMAN

ILSCO

SCHROFF

TRACHTE