

Novastar Cabinet With Glazed Door and Rear Panel

Energieversorger



Aluminum frame cabinets with attractive design, ideally suited for general electronics, test and measurement, audio/video and broadcasting applications.

ZERTIFIZIERUNGEN



EIGENSCHAFTEN

Type of protection IP 20

Cabinet width only 553 mm

Flush cladding parts

All uprights (front and rear) with 19" cut-outs

Bolted, die-cast frame with Al extrusions

With glass door (smoke grey) and rear panel

SPEZIFIKATIONEN

Table 1/3

Katalognummer	Rack Height	Frame Color	Höhe	Frame Color Code	Cladding Material	Breite
---------------	-------------	-------------	------	------------------	-------------------	--------

15230-019	12 U	Black Grey	589 mm	RAL 7021	Stahl	553 mm
16230-019	12 U	Black Grey	589 mm	RAL 7021	Stahl	553 mm
15230-020	16 U	Black Grey	767 mm	RAL 7021	Stahl	553 mm
16230-020	16 U	Black Grey	767 mm	RAL 7021	Stahl	553 mm
15230-021	20 U	Black Grey	945 mm	RAL 7021	Stahl	553 mm
16230-021	20 U	Black Grey	945 mm	RAL 7021	Stahl	553 mm
15230-022	38 U	Black Grey	1745 mm	RAL 7021	Stahl	553 mm
15230-023	38 U	Black Grey	1745 mm	RAL 7021	Stahl	553 mm
16230-022	38 U	Black Grey	1745 mm	RAL 7021	Stahl	553 mm
16230-023	38 U	Black Grey	1745 mm	RAL 7021	Stahl	553 mm
15230-024	43 U	Black Grey	1967 mm	RAL 7021	Stahl	553 mm
15230-025	43 U	Black Grey	1967 mm	RAL 7021	Stahl	553 mm
16230-024	43 U	Black Grey	1967 mm	RAL 7021	Stahl	553 mm
16230-025	43 U	Black Grey	1967 mm	RAL 7021	Stahl	553 mm

Table 2/3

Katalognummer	Cladding Color	Tiefe	Statische Last	Cladding Color Code	Konform mit	Frame Material
15230-019	Black Grey	600 mm	200 kgf	RAL 7021	IEC 60529, IEC 60297-3-100	Aluminium
16230-019	Light Grey	600 mm	200 kgf	RAL 7035	IEC 60529, IEC 60297-3-100	Aluminium
15230-020	Black Grey	600 mm	200 kgf	RAL 7021	IEC 60529, IEC 60297-3-100	Aluminium

Katalognummer	Cladding Color	Tiefe	Statische Last	Cladding Color Code	Konform mit	Frame Material
16230-020	Light Grey	600 mm	200 kgf	RAL 7035	IEC 60529, IEC 60297-3-100	Aluminium
15230-021	Black Grey	600 mm	200 kgf	RAL 7021	IEC 60529, IEC 60297-3-100	Aluminium
16230-021	Light Grey	600 mm	200 kgf	RAL 7035	IEC 60529, IEC 60297-3-100	Aluminium
15230-022	Black Grey	600 mm	400 kgf	RAL 7021	IEC 60529, IEC 60297-3-100	Aluminium
15230-023	Black Grey	800 mm	400 kgf	RAL 7021	IEC 60529, IEC 60297-3-100	Aluminium
16230-022	Light Grey	600 mm	400 kgf	RAL 7035	IEC 60529, IEC 60297-3-100	Aluminium
16230-023	Light Grey	800 mm	400 kgf	RAL 7035	IEC 60529, IEC 60297-3-100	Aluminium
15230-024	Black Grey	600 mm	400 kgf	RAL 7021	IEC 60529, IEC 60297-3-100	Aluminium
15230-025	Black Grey	800 mm	400 kgf	RAL 7021	IEC 60529, IEC 60297-3-100	Aluminium
16230-024	Light Grey	600 mm	400 kgf	RAL 7035	IEC 60529, IEC 60297-3-100	Aluminium
16230-025	Light Grey	800 mm	400 kgf	RAL 7035	IEC 60529, IEC 60297-3-100	Aluminium

Table 3/3

Katalognummer	Product Type	Protection Rating
15230-019	Schrank	IP20
16230-019	Schrank	IP20
15230-020	Schrank	IP20
16230-020	Schrank	IP20
15230-021	Schrank	IP20
16230-021	Schrank	IP20

Katalognummer	Product Type	Protection Rating
15230-022	Schrank	IP20
15230-023	Schrank	IP20
16230-022	Schrank	IP20
16230-023	Schrank	IP20
15230-024	Schrank	IP20
15230-025	Schrank	IP20
16230-024	Schrank	IP20
16230-025	Schrank	IP20

WARNUNG

nVent-Produkte müssen in Übereinstimmung mit den Produktinformationsblättern und dem Schulungsmaterial von nVent installiert und verwendet werden. Informationsblätter sind verfügbar unter www.nVent.com sowie bei Ihrem nVent-Kundendienstvertreter. Unsachgemäße Installation, Missbrauch, Fehlanwendung oder andere Handlungen im Widerspruch zu den Anweisungen und Warnungen von nVent können zu Fehlfunktionen, Anlagenschäden, schwerer Körperverletzung sowie zum Tod führen und/oder haben die Annullierung der Garantie zur Folge.



Our powerful portfolio of brands:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE