

LED Light Kit



LED light kits provide interior enclosure lighting suitable for remote and darkened enclosure applications. These light kits are light-weight and in a small form factor which are ideal where space is limited. The light can be mechanically fastened with included hardware to maintain enclosure UL listing (up to Type 4X), or can be magnetically attached to flat steel surfaces. The lights have auto-sensing circuitry (AC voltage 90 VAC to 265 VAC and DC voltage 20 VDC to 60 VDC). Option of a manual on/off switch or a PIR motion sensor is available.

MERKMALE

400 lumen at 120-degree angle of illumination

6000-7000K color temperature

Power consumption for all models is 5 watts

The power output allows up to 10 lights to be connected to each other (daisy chain)

Input and output connectors are included (16 AWG)

Operating temperature -22 F to 140 F (-30 C to 60 C)

Life expectancy of 60,000 hours at 68 F (20 C) under specifications

Protection Class II (double insulated)

SPEZIFIKATIONEN

Table 1/1						
Katalognummer	Material	Oberfläche	Farbe	Stromquelle	Befestigung	Eingabetyp
LEDD1S35	Kunststoff	Glatt-matt	Hellgrau	DC	Schraube	Ein-/Ausschalter
LEDA1S35	Kunststoff	Glatt-matt	Hellgrau	AC	Schraube	Ein-/Ausschalter
LEDD2S35	Kunststoff	Glatt-matt	Hellgrau	DC	Schraube	IR- Bewegungsmelder

WARNUNG

nVent-Produkte müssen in Übereinstimmung mit den Produktinformationsblättern und dem Schulungsmaterial von nVent installiert und verwendet werden. Informationsblätter sind verfügbar unter www.nVent.com sowie bei Ihrem nVent-Kundendienstvertreter. Unsachgemäße Installation, Missbrauch, Fehlanwendung oder andere Handlungen im Widerspruch zu den Anweisungen und Warnungen von nVent können zu Fehlfunktionen, Anlagenschäden, schwerer Körperverletzung sowie zum Tod führen und/oder haben die Annullierung der Garantie zur Folge.



Unser starkes markenportfolio:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE