

Flanschplatten für ProLine



Adjustable Gland Plates are used to seal the bottom of the ProLine frame. Solid, vented and shielded Gland Plates are available. Solid and filtered gland plates include covers that are gasketed to maintain Type 12 enclosure requirements. All installation hardware is included. Solid Gland Plate and EMC Gland Plate are accessories to 100-mm Solid Base, 100-mm/200-mm Plinth Base, Mobile Base and Transportation Base. These gland plates can be used without a base if casters, levelers or frame feet are installed. EMC Gland Plate maintains a Type 1 rating.

MERKMALE

Solid Gland Plate and EMC Gland Plate are accessories to 100-mm Solid Base, 100-mm/200-mm Plinth Base, Mobile Base and Transportation Base. These gland plates can be used without a base if casters, levelers or frame feet are installed.

Solid Gland Plate: the Solid Gland Plate can be used with all ProLine subpanels or rack angles. The gland plate consists of a base mounting surface and two adjustable foam-gasketed plates that permit cable entry. The plate can be rotated 180 degrees for front or rear cable entry.

EMC Gland Plate: This gland plate can be used with subpanels or rack angles. Gland plate consists of a base mounting surface and two adjustable gland plates (both have a conductive coating) with conductive fabric-over-foam gasket for cable entry.

Filtered (Vented) Gland Plate: Filtered Gland Plate is used only in conjunction with Vented Plinth Base Covers. The plate can be used with all ProLine subpanels or rack angles. It consists of a mounting base, three adjustable plates for cable entry, a filter and filter retaining rails. Manufactured from 16 gauge steel and finished with RAL 7035 textured light-gray polyester powder paint. Replacement filters available. EMC Gland Plate maintains a Type 1 rating.

All hardware included

SPEZIFIKATIONEN

Dicke: 1.9mm
Farbe: Hellgrau
Farbcode: RAL 7035

Table 1/1

Katalognummer	Material	Passend für Rahmenbreite	Passend für Rahmentiefe	Oberfläche	Schnelles Schiff
PGP66	Baustahl	600mm	600mm	Pulverbeschichtet	No
PGPV66	Baustahl	600mm	600mm	Pulverbeschichtet	No
PGPV68	Baustahl	600mm	800mm	Pulverbeschichtet	No
PGP68	Baustahl	600mm	800mm	Pulverbeschichtet	No
PGPV85	Baustahl	800mm	500mm	Pulverbeschichtet	No
PGP85	Baustahl	800mm	500mm	Pulverbeschichtet	No
PGPV88	Baustahl	800mm	800mm	Pulverbeschichtet	No
PGP88	Baustahl	800mm	800mm	Pulverbeschichtet	No
PGPV64	Baustahl	600mm	400mm	Pulverbeschichtet	No
PGP64	Baustahl	600mm	400mm	Pulverbeschichtet	No
PGPV86	Baustahl	800mm	600mm	Pulverbeschichtet	No
PGP86	Baustahl	800mm	600mm	Pulverbeschichtet	No
PGP105	Baustahl	1000mm	500mm	Pulverbeschichtet	No
PGPV106	Baustahl	1000mm	600mm	Pulverbeschichtet	No
PGP106	Baustahl	1000mm	600mm	Pulverbeschichtet	No
PGPV108	Baustahl	1000mm	800mm	Pulverbeschichtet	No

Katalognummer	Material	Passend für Rahmenbreite	Passend für Rahmentiefe	Oberfläche	Schnelles Schiff
PGP108	Baustahl	1000mm	800mm	Pulverbeschichtet	No
PGP84	Baustahl	800mm	400mm	Pulverbeschichtet	No
PGPV65	Baustahl	600mm	500mm	Pulverbeschichtet	No
PGP65	Baustahl	600mm	500mm	Pulverbeschichtet	No
PGPV76	Baustahl	700mm	600mm	Pulverbeschichtet	No
PGP78	Baustahl	700mm	800mm	Pulverbeschichtet	No
PGPV78	Baustahl	700mm	800mm	Pulverbeschichtet	No
PGPV89	Baustahl	800mm	900mm	Pulverbeschichtet	No
PGP89	Baustahl	800mm	900mm	Pulverbeschichtet	No
PGP79	Baustahl	700mm	900mm	Pulverbeschichtet	No
PGP104	Baustahl	1000mm	400mm	Pulverbeschichtet	No
PGP105AHF	Baustahl	1000mm	500mm	Verzinkt	No
PGP108AHF	Baustahl	1000mm	800mm	Verzinkt	No
PGP124	Baustahl	1200mm	400mm	Pulverbeschichtet	No
PGP125	Baustahl	1200mm	500mm	Pulverbeschichtet	No
PGP126	Baustahl	1200mm	600mm	Pulverbeschichtet	No
PGP128	Baustahl	1200mm	800mm	Pulverbeschichtet	No
PGP164	Baustahl	1600mm	400mm	Pulverbeschichtet	No
PGP165	Baustahl	1600mm	500mm	Pulverbeschichtet	No
PGP166	Baustahl	1600mm	600mm	Pulverbeschichtet	No

Katalognummer	Material	Passend für Rahmenbreite	Passend für Rahmentiefe	Oberfläche	Schnelles Schiff
PGP168	Baustahl	1600mm	800mm	Pulverbeschichtet	No
PGP185	Baustahl	1800mm	500mm	Pulverbeschichtet	No
PGP186	Baustahl	1800mm	600mm	Pulverbeschichtet	No
PGP188	Baustahl	1800mm	800mm	Pulverbeschichtet	No
PGP45	Baustahl	400mm	500mm	Pulverbeschichtet	No
PGP46	Baustahl	400mm	600mm	Pulverbeschichtet	No
PGP64AHF	Baustahl	600mm	400mm	Verzinkt	No
PGP65AHF	Baustahl	600mm	500mm	Verzinkt	No
PGP66AHF	Baustahl	600mm	600mm	Verzinkt	No
PGP68AHF	Baustahl	600mm	800mm	Verzinkt	No
PGP78AHF	Baustahl	700mm	800mm	Verzinkt	No
PGP79AHF	Baustahl	700mm	900mm	Verzinkt	No
PGP88AHF	Baustahl	800mm	800mm	Verzinkt	No
PGP89AHF	Baustahl	800mm	900mm	Verzinkt	No
PGPV125	Baustahl	1200mm	500mm	Pulverbeschichtet	No
PGPV126	Baustahl	1200mm	600mm	Pulverbeschichtet	No
PGPV128	Baustahl	1200mm	800mm	Pulverbeschichtet	No
PGPV165	Baustahl	1600mm	500mm	Pulverbeschichtet	No
PGPV166	Baustahl	1600mm	600mm	Pulverbeschichtet	No

WARNUNG

nVent-Produkte müssen in Übereinstimmung mit den Produktinformationsblättern und dem Schulungsmaterial von nVent installiert und verwendet werden. Informationsblätter sind verfügbar unter www.nVent.com sowie bei Ihrem nVent-Kundendienstvertreter. Unsachgemäße Installation, Missbrauch, Fehlanwendung oder andere Handlungen im Widerspruch zu den Anweisungen und Warnungen von nVent können zu Fehlfunktionen, Anlagenschäden, schwerer Körperverletzung sowie zum Tod führen und/oder haben die Annullierung der Garantie zur Folge.



Unser starkes markenportfolio:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE