

nVent ERIFLEX Flexbus HCBC Plate with PE Connection



CERTIFICERINGER



FUNKTIONER

Rigid tinned copper part provides strong electrical contact to maintain braid expansion during compression

HCBC Plate allows Flexbus Conductor insulation to overlap the connection palm

HCBC Plate with PE connection allows conductor to be added to interconnect neutral and ground/earth

Tinned copper allows for copper or aluminum conductor connections

Installs quickly and easily

RoHS compliant

SPECIFIKATIONER

Materiale: Copper

Finish: Tinned

Table 1/2

Katalognummer	Artikelnummer	A	B	C	D	E
---------------	---------------	---	---	---	---	---

FLEXPLATE50PE	508182	65 mm	100 mm	45 mm	41 mm	70 mm
FLEXPLATE100PE	508183	115 mm	100 mm	45 mm	51 mm	70 mm


Table 2/2

Katalognummer	Artikelnummer	Hole Size 1 (HS1)	Hole Size 2 (HS2)	Thickness (T)	Conductor Size	Unit Weight
FLEXPLATE50PE	508182	10.5 mm	14.5 mm	5 mm	220 mm ² , 360 mm ² , 545 mm ² , 640 mm ²	0.49 kg
FLEXPLATE100PE	508183	12.5 mm	18.5 mm	5 mm	960 mm ² , 1280 mm ² , 1810 mm ²	0.71 kg

YDERLIGERE PRODUKTOPLYSNINGER

It is mandatory to use the HCBC Clamp associated with the HCBC Plate for proper Flexbus Conductor connection.

DIAGRAMS



ADVARSEL

nVent-produkter skal kun installeres og anvendes som angivet i nVents produktvejledninger og træningsmaterialer. Vejledninger er tilgængelige på www.nvent.com og hos din nVent kundeservicerepræsentant. Forkert installation, misbrug, fejlanvendelse eller anden undladelse af fuldt ud at følge nVents instruktioner og advarsler kan medføre funktionsfejl, materielle skader, alvorlige personskader eller død og/eller ugyldiggøre din garanti.

North America

+1.800.753.9221

Option 1 – Customer Care

Option 2 – Technical

Support

Europe

Netherlands:

+31 800-0200135

France:

+33 800 901 793

Europe

Germany:

800 1890272

Other Countries:

+31 13 5835404

APAC

Shanghai:

+ 86 21 2412 1618/19

Sydney:

+61 2 9751 8500



Vores kraftfulde portefølje af mærker:

CADDY

ERICO

HOFFMAN

ILSCO

SCHROFF

TRACHTE