

## Seismic Plinth Base, PSB-Z4



Plinth base for seismic zones. The PSB-Z4 adds height, convenient cable management and rigidity, enabling the enclosure to withstand vibrations with accelerations up to 1.6 g in all directions. This meets all requirements for Telcordia GR-63-CORE, Zone 4.

### MERKMALE

---

Description: Seismic Plinth base to be added to standard MCS enclosures to be used in a Seismic Zone 4 rating.

Pack Qty: 1 Assembly per order.

## SPEZIFIKATIONEN

Table 1/1

| Katalognummer | Höhe  | Breite | Tiefe | Material | Farbcode | Anzahl Verpackungen |
|---------------|-------|--------|-------|----------|----------|---------------------|
| PSB0806Z4     | 100mm | 800mm  | 600mm | Baustahl | RAL 7022 | 1                   |
| PSB1008Z4     | 100mm | 1000mm | 800mm | Baustahl | RAL 7022 | 1                   |
| PSB0606Z4     | 100mm | 600mm  | 600mm | Baustahl | RAL 7022 | 1                   |
| PSB0604Z4     | 100mm | 600mm  | 400mm | Baustahl | RAL 7022 | 1                   |
| PSB0808Z4     | 100mm | 800mm  | 800mm | Baustahl | RAL 7022 | 1                   |

## WARNUNG

nVent-Produkte müssen in Übereinstimmung mit den Produktinformationsblättern und dem Schulungsmaterial von nVent installiert und verwendet werden. Informationsblätter sind verfügbar unter [www.nVent.com](http://www.nVent.com) sowie bei Ihrem nVent-Kundendienstvertreter. Unsachgemäße Installation, Missbrauch, Fehlanwendung oder andere Handlungen im Widerspruch zu den Anweisungen und Warnungen von nVent können zu Fehlfunktionen, Anlagenschäden, schwerer Körperverletzung sowie zum Tod führen und/oder haben die Annullierung der Garantie zur Folge.



Unser starkes markenportfolio:

**CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE**