

# 19" Pusher Fan, 2 U, Axial

## Energieversorger

Fan tray with integrated pusher fan.



### ZERTIFIZIERUNGEN



### EIGENSCHAFTEN

Contact protection in accordance with DIN EN ISO 13857

Integrated air deflector prevents heat buildup in the assemblies mounted below

Can be adapted to subracks

Optionally with additional rear fan, 2 U, for active cooling of assemblies beneath the pusher fan

### SPEZIFIKATIONEN

Table 1/1

| Katalognummer | Input Voltage AC | Input Voltage DC |
|---------------|------------------|------------------|
| 10713-518     | 230 V min        |                  |
| 10713-520     | 115 V min        |                  |

| Katalognummer | Input Voltage AC | Input Voltage DC |
|---------------|------------------|------------------|
| 10713-526     | 230 V min        |                  |
| 10713-534     | 230 V min        |                  |
| 10713-536     | 115 V min        |                  |
| 10713-529     |                  | 24 V min         |
| 10713-537     |                  | 24 V min         |
| 19713-540     |                  |                  |

## ADDITIONAL PRODUCT DETAILS

Please order mains cable separately.

## WARNUNG

nVent-Produkte müssen in Übereinstimmung mit den Produktinformationsblättern und dem Schulungsmaterial von nVent installiert und verwendet werden. Informationsblätter sind verfügbar unter [www.nVent.com](http://www.nVent.com) sowie bei Ihrem nVent-Kundendienstvertreter. Unsachgemäße Installation, Missbrauch, Fehlanwendung oder andere Handlungen im Widerspruch zu den Anweisungen und Warnungen von nVent können zu Fehlfunktionen, Anlagenschäden, schwerer Körperverletzung sowie zum Tod führen und/oder haben die Annullierung der Garantie zur Folge.



Our powerful portfolio of brands:

**CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE**