

MultipacPRO 19" Chassis, Aluminum, Perforated Top and Base

Energieversorger



This 19" chassis is a form of subrack which accepts horizontal board mounting or the mounting of non-standard components like transformers or other heavy load accessories typically mounted on a chassis plate. This version have perforated top and bottom cover for better air flow and heat dissipation.

ZERTIFIZIERUNGEN



EIGENSCHAFTEN

Aluminum construction

Detachable front and rear panel for easy machining

IP 20, in accordance with IEC 60529

Supplied as space-saving flat-pack

Modifications such as cutouts, different finishes or dimensions available

Internal and external dimensions in accordance with: IEC 60297-3-100, -105

EMC shielding: Approx. 20dB(A) at 2 GHz without shielding material. >40dB(A) at 1 GHz with addition of stainless steel gasket between front panel and case body

SPEZIFIKATIONEN

Table 1/2

Katalognummer	Rack Height	Tiefe	Usable Width	Montage	Konform mit	EMC Shielding
20860-621	1 U	220 mm	403 mm	Rack	IEC 60297-3-100, IEC 60297-3-105	No (Retrofittable)
20860-622	1 U	280 mm	403 mm	Rack	IEC 60297-3-100, IEC 60297-3-105	No (Retrofittable)
20860-624	2 U	220 mm	4 mm	Rack	IEC 60297-3-100	No (Retrofittable)
20860-625	2 U	280 mm	403 mm	Rack	IEC 60297-3-100	No (Retrofittable)
20860-626	2 U	340 mm	403 mm	Rack	IEC 60297-3-100	No (Retrofittable)
20860-627	3 U	280 mm	403 mm	Rack	IEC 60297-3-100	No (Retrofittable)
20860-628	3 U	340 mm	403 mm	Rack	IEC 60297-3-100	No (Retrofittable)
20860-629	3 U	400 mm	403 mm	Rack	IEC 60297-3-100	No (Retrofittable)
20860-630	3 U	460 mm	4 mm	Rack	IEC 60297-3-100	No (Retrofittable)
20860-632	4 U	340 mm	403 mm	Rack	IEC 60297-3-100	No (Retrofittable)
20860-633	4 U	400 mm	403 mm	Rack	IEC 60297-3-100	No (Retrofittable)
20860-634	4 U	460 mm	403 mm	Rack	IEC 60297-3-100	No (Retrofittable)
20860-635	5 U	460 mm	403 mm	Rack	IEC 60297-3-100	No (Retrofittable)

Table 2/2

Katalognummer	Product Family	Product Type	Typ	Zertifizierungen
20860-621	MultipacPRO	Subrack/Chassis	Perforiert	RoHS
20860-622	MultipacPRO	Subrack/Chassis	Perforiert	RoHS
20860-624	MultipacPRO	Subrack/Chassis	Perforiert	

Katalognummer	Product Family	Product Type	Typ	Zertifizierungen
20860-625	MultipacPRO	Subrack/Chassis	Perforiert	RoHS
20860-626	MultipacPRO	Subrack/Chassis	Perforiert	RoHS
20860-627	MultipacPRO	Subrack/Chassis	Perforiert	RoHS
20860-628	MultipacPRO	Subrack/Chassis	Perforiert	RoHS
20860-629	MultipacPRO	Subrack/Chassis	Perforiert	RoHS
20860-630	MultipacPRO	Subrack/Chassis	Perforiert	
20860-632	MultipacPRO	Subrack/Chassis	Perforiert	RoHS
20860-633	MultipacPRO	Subrack/Chassis	Perforiert	RoHS
20860-634	MultipacPRO	Subrack/Chassis	Perforiert	RoHS
20860-635	MultipacPRO	Subrack/Chassis	Perforiert	RoHS

ADDITIONAL PRODUCT DETAILS

Please order front handles separately.

WARNUNG

nVent-Produkte müssen in Übereinstimmung mit den Produktinformationsblättern und dem Schulungsmaterial von nVent installiert und verwendet werden. Informationsblätter sind verfügbar unter www.nVent.com sowie bei Ihrem nVent-Kundendienstvertreter. Unsachgemäße Installation, Missbrauch, Fehlanwendung oder andere Handlungen im Widerspruch zu den Anweisungen und Warnungen von nVent können zu Fehlfunktionen, Anlagenschäden, schwerer Körperverletzung sowie zum Tod führen und/oder haben die Annullierung der Garantie zur Folge.



Our powerful portfolio of brands:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE