

# Universal Transient Barrier, Single Pair LED



## CERTIFICATIONS



## FEATURES

LED status indication and voltage-free contacts provide remote status monitoring

Multi-stage protection and fine over-voltage protection helps ensure lowest residual surge voltages reach sensitive equipment

Common-mode and differential-mode protection protects against both possible surge conditions

Surge rating to 20 kA 8/20  $\mu$ s is ideal for exposed wiring

## SPECIFICATIONS


| Catalog Number                        | UTB30SPLED                 |
|---------------------------------------|----------------------------|
| Nominal System Voltage (Un)           | 10 - 21 VAC<br>15 - 30 VDC |
| Max Continuous Operating Voltage (Uc) | 23 VAC<br>33 VDC           |
| Rated Load Current (IL)               | 2A                         |
| Frequency                             | 2 Hz                       |
| Loop Resistance                       | 1 $\Omega$                 |

| Catalog Number                                    | UTB30SPLED                                                                              |
|---------------------------------------------------|-----------------------------------------------------------------------------------------|
| Max Discharge Current (I <sub>max</sub> ), L+L-PE | 20kA 8/20 μs                                                                            |
| Protection Modes                                  | Common<br>Differential                                                                  |
| Power Supply Voltage                              | 24                                                                                      |
| Status Indication                                 | LED                                                                                     |
| Status Indication Operating Voltage               | 18 - 42                                                                                 |
| Technology                                        | Gas Discharge Tube (GDT)<br>Metal Oxide Varistor (MOV)<br>Silicon Avalanche Diode (SAD) |
| Voltage Protection Level (U <sub>p</sub> ), L-L   | 44 V @ 3 kA                                                                             |
| Connection, Stranded                              | 1 - 4 mm <sup>2</sup>                                                                   |
| Mounting                                          | 35 mm top hat DIN rail                                                                  |
| Temperature                                       | -20 to 65 °C                                                                            |
| Enclosure Material                                | UL® 94V-0 Thermoplastic                                                                 |
| Enclosure Rating                                  | IP 20<br>NEMA®-1                                                                        |
| Depth (D)                                         | 85mm                                                                                    |
| Height (H)                                        | 90 mm                                                                                   |
| Width (W)                                         | 12 mm                                                                                   |
| Unit Weight                                       | 0.02 kg                                                                                 |
| Complies With                                     | ANSI®/IEEE® C62.41.2-2002 Cat A, Cat B, Cat C                                           |
| Replacement Module                                | UTB30SPLEDM                                                                             |

## ADDITIONAL PRODUCT DETAILS

Indicated power supply voltage is for LED status indication.

## DIAGRAMS



**WARNING**

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at [www.nvent.com](http://www.nvent.com) and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.

**North America**

+1.800.753.9221  
Option 1 – Customer Care  
Option 2 – Technical  
Support

**Europe**

Netherlands:  
+31 800-0200135  
France:  
+33 800 901 793

**Europe**

Germany:  
800 1890272  
Other Countries:  
+31 13 5835404

**APAC**

Shanghai:  
+ 86 21 2412 1618/19  
Sydney:  
+61 2 9751 8500



Our powerful portfolio of brands:

**CADDY   ERICO   HOFFMAN   ILSCO   SCHROFF   TRACHTE**