

AT-TS Surface Sensing Thermostat



nVent RAYCHEM AT-TS Thermostats are electronic line or ambient sensing thermostats for self-regulating heating cables in pipe freeze protection or temperature maintenance applications.

FEATURES

Energy saving, line-sensing or ambient electronic control thermostat.

Adjustable: -5 °C to +15 °C (AT-TS-13), 0 °C to +120 °C (AT-TS-14)

Direct switching of heating cables, maximum current 16 A, 250 VAC

Simple and fast to install

Easy to use: LEDs indicate when cables are energized or when temperature sensor is defective

Reliable during long life: 6 year extended product warranty available, maintenance free

SPECIFICATIONS

Depth: 55 mmHeight: 120 mmWidth: 122 mmIP Rating: IP65

Table 1/1		
Catalog Number	Item Name	Temperature Control Range
648945-000	AT-TS-14	0 - 120 °C
728129-000	AT-TS-13	−5 to 15 °C

WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper

installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.

North America

Tel +1.800.545.6258 Fax +1.800.527.5703 thermal.info@nvent.com Europe, Middle East, Africa

Tel +32.16.213.511 Fax +32.16.213.604 thermal.info@nvent.com **Asia Pacific**

Tel +86.21.2412.1688 Fax +86.21.5426.3167 cn.thermal.info@nvent.com **Latin America**

Tel +1.713.868.4800 Fax +1.713.868.2333 thermal.info@nvent.com