

# **Busbar Adapter 25A Without Cables, W060**



Busbar adapter with one mounting rail with screw terminals 6 mm<sup>2</sup>.

### **INDUSTRY STANDARDS**

UL

CSA

GL

### **FEATURES**

Description: Busbar adapter 25 A. With two adjustable mounting rails. With screw terminals 6 mm² from the rear.

Rated voltage: 690 V

Rated current: 25 A

For busbars: 12, 15, 20, 25,  $30 \times 5$ , 10

Power dissipation at 80% load: 1.2 W

Poles: 3-pole

Dimensions:  $45 \times 200 \times 63$  mm

Pack quantity: 1 pc.

Approvals: CSA, UL, GL

### **SPECIFICATIONS**

Table 1/1						
Catalog Number	Height	Width	Depth	Material	Finish	Color
32436	45mm	200mm	75mm	Plastic, Mild Steel	Plated	Black, Light Gray

## **WARNING**

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.



Our powerful portfolio of brands:

**CADDY ERICO HOFFMAN TRACHTE ILSCO SCHROFF**