



Adjustable Monitor Arm

CATALOG NUMBER

60118-562



The collapsible articulate arm is ideal for a rack mounted stand workstation. It's an easy to install, rack-mountable appendage which allows for panoramic movement possibilities for a flat panel monitor in industrial environments

FEATURES

Support arm for mounting of flat panel monitor

Vesa Adapter 75x75 and 100x100 mm; Monitor size which can be mounted are of maximum "32

Fixing is to the side of the frame

Static load-carrying capacity (10 kg max.)

Support arm: Height-adjustable 300 mm; Angle of rotation on cabinet 180°; Monitor rotation angle 340° (fitted on cabinet 270°); Monitor tilt angle 60°; Integrated cable routing

Suitable for industrial and laboratory applications

PRODUCT ATTRIBUTES

Product Type: Monitor Arm

Works With: Cabinet

Material: Steel; Aluminum; Plastic

Net Weight: 2.85kg

Package Quantity: 1

WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.

North America

All locations
+1.763.422.2661
Chat with us:
nvent.com/schroff

Europe

Straubenhardt, Germany
+49.7082.794.0
Betschdorf, France
+33.3.88.90.64.90
Warsaw, Poland
+48.22.209.98.35
Assago, Italy
+39.02.932.7141
Chat with us:
nvent.com/schroff

Asia

Shanghai, China
+86.21.2412.6943
Qingdao, China
+86.532.8771.6101
Singapore
+65.6768.5800
Shin-Yokohama, Japan
+81.45.476.0271
Chat with us:
nvent.com/schroff

Middle East & India

Dubai, United Arab
Emirates
+971.4.378.1700
Bangalore, India
+91.80.6715.2001
Istanbul, Turkey
+90.216.250.7374
Chat with us:
nvent.com/schroff



Our powerful portfolio of brands:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE