


Front Panel, Shielded, Side Hinged, 3 U, 84 HP, 2.5 mm, Al, Front Anodized, Rear Conductive

CATALOG NUMBER

20848-611



Front panel with textile EMC gasket, side hinged assembly.

CERTIFICATIONS



FEATURES

Front panel with textile EMC gasket

Enables mounting onto the horizontal rails

Suitable for subracks and cases

Hinges can be fitted on left or right

Rack Height: 3U
Package Quantity: 1
Accessory Type: Front panel
Mounting: Hinged, Side
Gasket Type: Textile EMC
Front Finish: Anodized
Rear Finish: Conductive
Treated Edges: No
Depth (D): 2.5mm
EMC Shielding: No (Retrofittable)
Finish: Anodized; Passivated
Height (H): 128.4mm
Material: Aluminum
Product Type: Front Panel
Rack Width: 84HP
Type: Front Panel without Handle
Width (W): 426.4mm
Net Weight: 0.56kg

The drawing consists of three views of a mechanical part:

- Side View (Left):** Shows a horizontal plate of width W and height h . A vertical dimension line indicates a distance of 2 TE from the left edge to the center of the plate. A diagonal line is shown at an angle of 90° to the horizontal, with a 180° arc indicating a full rotation.
- Front View (Right):** Shows a rectangular plate with overall width W and height H . The top edge has a dimension of 11.4 . The bottom edge has a dimension of 2.5 . The right edge has a dimension of 7.45 . The left edge has a dimension of 12.1 . A hole with diameter $\varnothing 5.9 \times 3.3$ is located in the upper right quadrant. A hole with diameter $\varnothing 2.7$ is located in the lower left quadrant. A coordinate system with X and Y axes is shown at the bottom left corner.
- Cross-section X (Bottom Left):** A circular cross-section with diameter $\varnothing 2.5$. It shows a central hole with diameter $\varnothing 2.5$ and a thickness of 2.5 .
- Cross-section Y (Bottom Right):** A circular cross-section with diameter $\varnothing 2.5$. It shows a central hole with diameter $\varnothing 2.5$ and a thickness of 2.5 .

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.

North America

All locations
+1.763.422.2661
Chat with us:
nvent.com/schroff

Europe

Straubenhardt, Germany
+49.7082.794.0
Betschdorf, France
+33.3.88.90.64.90
Warsaw, Poland
+48.22.209.98.35
Assago, Italy
+39.02.932.7141
Chat with us:
nvent.com/schroff

Asia

Shanghai, China
+86.21.2412.6943
Qingdao, China
+86.532.8771.6101
Singapore
+65.6768.5800
Shin-Yokohama, Japan
+81.45.476.0271
Chat with us:
nvent.com/schroff

Middle East & India

Dubai, United Arab Emirates
+971.4.378.1700
Bangalore, India
+91.80.6715.2001
Istanbul, Turkey
+90.216.250.7374
Chat with us:
nvent.com/schroff



Our powerful portfolio of brands:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE