


Crossboard Mounting Platform, WOCB



Connection and mounting platform for all CrossBoard components.

INDUSTRY STANDARDS

UL

IEC

FEATURES

Description: 3-pole modular power distribution system, with touch safe protection. Mounting platform for all CrossBoard components.

Rated voltage: 690 V.

Rated current: 125 A.

Power dissipation at 80% load: 3.4 W (11225), 6 W (11405).

Pack quantity: 1 pc.

Approvals: IEC, UL.

SPECIFICATIONS

Table 1/1						
Catalog Number	Height	Width	Enclosure Material	Product Family	Material	Finish
11225	160mm	225mm	Plastic	IEC General Accessories	Plastic	Smooth Matte
11405	160mm	405mm	Plastic	IEC General Accessories	Plastic	Smooth Matte

WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.



Our powerful portfolio of brands:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE