

# nVent ERICO Hammerlock Ground Clamp



The nVent ERICO Hammerlock irreversible mechanical connection connects the grounding conductor to the ground rod. Machined from highly conductive copper, the state-of-the-art Hammerlock provides a low resistance connection designed to withstand ground fault currents and lightning transients. The connector's mechanically rugged design will help ensure that the highest level of performance is maintained for many years after the connection has been buried in the harsh underground environment.

Installing the Hammerlock is as easy as swinging a hammer and requires no special tools or training. The Hammerlock can be installed three to five times faster than an acorn clamp and provides a high-quality grounding connection that is easy to use and withstands 100% of the current carrying capacity of the conductor.

## CERTIFICATIONS



## FEATURES

Irreversible connection with excellent mechanical strength

Fast and simple installation requires only a hammer

No special training required

Low resistance connection

Provides a visual indication of completed connection

Allows for "T" or pass-through connections

Suitable for Copperweld® steel conductors

## SPECIFICATIONS


**Material:** Copper

Table 1/1

| Catalog Number | Ground Rod Type | Ground Rod Diameter, Nominal | Ground Rod Diameter, Actual (Ø) | Conductor Size                                                   | Number of Conductors | Certifications |
|----------------|-----------------|------------------------------|---------------------------------|------------------------------------------------------------------|----------------------|----------------|
| EHL12FC1K      | Copper-bonded   | 1/2"                         | 12.7 mm                         | #6 Solid - #4 Solid, 16 mm <sup>2</sup> Stranded                 | 1                    | UL, cUL        |
| EHL12FC1K1K    | Copper-bonded   | 1/2"                         | 12.7 mm                         | #6 Solid - #4 Solid, 16 mm <sup>2</sup> Stranded                 | 2                    |                |
| EHL12FC1V      | Copper-bonded   | 1/2"                         | 12.7 mm                         | #4 Stranded - #2 Stranded, 25 mm <sup>2</sup> Stranded           | 1                    | cUL, UL        |
| EHL12FC2G      | Copper-bonded   | 1/2"                         | 12.7 mm                         | 1/0 Stranded - 2/0 Stranded                                      | 1                    | UL, cUL        |
| EHL58C1K       | Copper-bonded   | 5/8"                         | 14.2 mm                         | #6 Solid - #4 Solid, 16 mm <sup>2</sup> Stranded, #2 Solid       | 1                    | cUL, RUS, UL   |
| EHL58C1K1K     | Copper-bonded   | 5/8"                         | 14.2 mm                         | #6 Solid - #4 Solid, 16 mm <sup>2</sup> Stranded                 | 2                    | UL, cUL        |
| EHL58C1V       | Copper-bonded   | 5/8"                         | 14.2 mm                         | #4 Stranded - #2 Stranded, 25 mm <sup>2</sup> Stranded           | 1                    | cUL, UL        |
| EHL58C1V1V     | Copper-bonded   | 5/8"                         | 14.2 mm                         | #2 Solid - #2 Stranded, #2 Solid                                 | 2                    | UL, cUL        |
| EHL58C2G       | Copper-bonded   | 5/8"                         | 14.2 mm                         | 1/0 Stranded - 2/0 Stranded                                      | 1                    | cUL, UL        |
| EHL58C2Q       | Copper-bonded   | 5/8"                         | 14.2 mm                         | 3/0 Stranded - 4/0 Stranded, #2 Solid                            | 1                    | UL, cUL        |
| EHL58G1K       | Galvanized      | 5/8"                         | 16 mm                           | #6 Solid - #4 Solid, 16 mm <sup>2</sup> Stranded, #2 Solid       | 1                    | cUL, UL, RUS   |
| EHL58G1K1K     | Galvanized      | 5/8"                         | 16 mm                           | #6 Solid - #4 Solid, 16 mm <sup>2</sup> Stranded, #2 Solid       | 2                    |                |
| EHL58G1V       | Galvanized      | 5/8"                         | 16 mm                           | #4 Stranded - #2 Stranded, 25 mm <sup>2</sup> Stranded, #2 Solid | 1                    | cUL, UL        |

| CatalogNumber | Ground Rod Type | Ground Rod Diameter, Nominal | Ground Rod Diameter, Actual (Ø) | Conductor Size                                             | Number of Conductors | Certifications |
|---------------|-----------------|------------------------------|---------------------------------|------------------------------------------------------------|----------------------|----------------|
| EHL58G2G      | Galvanized      | 5/8"                         | 16 mm                           | 1/0 Stranded - 2/0 Stranded, #2 Solid                      | 1                    | UL, cUL        |
| EHL34C1K      | Copper-bonded   | 3/4"                         | 17.3 mm                         | #6 Solid - #4 Solid, 16 mm <sup>2</sup> Stranded           | 1                    | cUL, UL        |
| EHL34C1V      | Copper-bonded   | 3/4"                         | 17.3 mm                         | #4 Stranded - #2 Stranded, 25 mm <sup>2</sup> Stranded     | 1                    | UL, cUL        |
| EHL34C2G      | Copper-bonded   | 3/4"                         | 17.3 mm                         | 1/0 Stranded - 2/0 Stranded, #2 Solid                      | 1                    | cUL, UL        |
| EHL34C2Q      | Copper-bonded   | 3/4"                         | 17.3 mm                         | 3/0 Stranded - 4/0 Stranded, #2 Solid                      | 1                    | UL, cUL        |
| EHL34G1K      | Galvanized      | 3/4"                         | 18.5 mm                         | #6 Solid - #4 Solid, 16 mm <sup>2</sup> Stranded, #2 Solid | 1                    | cUL, UL        |

## DIAGRAMS



## WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at [www.nvent.com](http://www.nvent.com) and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.

⚠ WARNING: This product can expose you to chemicals including lead, which is known to the State of California to cause cancer and birth defects or other reproductive harm. For more information go to [www.P65Warnings.ca.gov](http://www.P65Warnings.ca.gov).

#### North America

+1.800.753.9221

Option 1 – Customer Care

Option 2 – Technical

Support

#### Europe

Netherlands:

+31 800-0200135

France:

+33 800 901 793

#### Europe

Germany:

800 1890272

Other Countries:

+31 13 5835404

#### APAC

Shanghai:

+ 86 21 2412 1618/19

Sydney:

+61 2 9751 8500



Our powerful portfolio of brands:

**CADDY**

**ERICO**

**HOFFMAN**

**ILSCO**

**SCHROFF**

**TRACHTE**