


# MI Series Alloy 825 XMI-A HAx Heating Cable



nVent RAYCHEM XMI-A mineral insulated (MI) series resistance trace heating cables provide freeze protection and process temperature maintenance on pipes/vessels up to 1022 °F/550 °C and intermittent exposure to 1200 °F/650 °C. Available with 300 V and 600 V rating, approved for applications up to 61 W/ft (200 W/m) and hazardous areas. The Alloy 825 sheath provides extreme resistance to a broad range of corrosive environments.

## FEATURES

Reliable during long life: 10 year product warranty available, robust and rugged construction, proven in harsh climates extends life expectancy

Reduced total installed cost

Dual conductor versions particularly suited to small pipes and instrument tubing

Reduced power supply costs: lower start up currents compared with other technologies

Simple controls: current monitoring on series resistance provides instant visibility on critical circuits

Fast track / expedite service for configured heating units for eligible designs

Excellent corrosion resistance to a wide range of organic acids, alkalis and chloride stress-corrosion cracking

## SPECIFICATIONS

|                                                        |                           |
|--------------------------------------------------------|---------------------------|
| <b>Max Continuous Exposure Temperature, Power Off:</b> | 650 °C                    |
| <b>Min Installation Temperature:</b>                   | -60 °C                    |
| <b>Sheath Material:</b>                                | Alloy 825                 |
| <b>Area Classification:</b>                            | Non-Hazardous; Hazardous  |
| <b>Insulation Material:</b>                            | Magnesium Oxide           |
| <b>Ground Path Type:</b>                               | Sheath                    |
| <b>Conductor Material:</b>                             | Various Alloys and Copper |

Table 1/1

| Catalog Number | Supply Voltage | Max Power Output | Conductor Quantity | Nominal Resistance @ 20°C | Outer Diameter |
|----------------|----------------|------------------|--------------------|---------------------------|----------------|
|----------------|----------------|------------------|--------------------|---------------------------|----------------|

|          |           |         |   |           |         |
|----------|-----------|---------|---|-----------|---------|
| 61SC6640 | 0 – 600 V | 200 W/m | 1 | 2 Ω/km    | 8.1 mm  |
| 61SC5102 | 0 – 600 V | 200 W/m | 1 | 3.3 Ω/km  | 6.4 mm  |
| 62SC5128 | 0 – 600 V | 270 W/m | 2 | 4.3 Ω/km  | 13.8 mm |
| 61SC5162 | 0 – 600 V | 200 W/m | 1 | 5.3 Ω/km  | 6.8 mm  |
| 62SC5204 | 0 – 600 V | 270 W/m | 2 | 6.6 Ω/km  | 12.6 mm |
| 61SC5258 | 0 – 600 V | 200 W/m | 1 | 8.5 Ω/km  | 5.5 mm  |
| 62SC5324 | 0 – 600 V | 270 W/m | 2 | 10.5 Ω/km | 10.2 mm |
| 61SC5409 | 0 – 600 V | 200 W/m | 1 | 13.5 Ω/km | 4.9 mm  |
| 62SC5516 | 0 – 600 V | 270 W/m | 2 | 17 Ω/km   | 9.2 mm  |
| 61SC5651 | 0 – 600 V | 200 W/m | 1 | 21.3 Ω/km | 4.7 mm  |
| 62SC5818 | 0 – 600 V | 270 W/m | 2 | 27 Ω/km   | 8.4 mm  |
| 61SP4113 | 0 – 600 V | 200 W/m | 1 | 37 Ω/km   | 4.7 mm  |
| 62SC4130 | 0 – 600 V | 270 W/m | 2 | 43 Ω/km   | 7.7 mm  |
| 61SP4145 | 0 – 600 V | 200 W/m | 1 | 48 Ω/km   | 4.3 mm  |
| 61SP4183 | 0 – 600 V | 200 W/m | 1 | 60 Ω/km   | 4.3 mm  |
| 62SC4200 | 0 – 600 V | 270 W/m | 2 | 66 Ω/km   | 7.2 mm  |
| 61SP4231 | 0 – 600 V | 200 W/m | 1 | 76 Ω/km   | 4.4 mm  |
| 62SP4281 | 0 – 600 V | 270 W/m | 2 | 92 Ω/km   | 7.4 mm  |
| 61SP4290 | 0 – 600 V | 200 W/m | 1 | 95 Ω/km   | 4.5 mm  |

|          |           |         |   |            |        |
|----------|-----------|---------|---|------------|--------|
| 32SC4324 | 0 – 300 V | 200 W/m | 2 | 105 Ω/km   | 4.7 mm |
| 32SA2400 | 0 – 300 V | 200 W/m | 2 | 13200 Ω/km | 3.7 mm |
| 61SP4366 | 0 – 600 V | 200 W/m | 1 | 120 Ω/km   | 4.4 mm |
| 32SA2275 | 0 – 300 V | 200 W/m | 2 | 9000 Ω/km  | 3.9 mm |
| 32SF1110 | 0 – 300 V | 200 W/m | 2 | 36000 Ω/km | 4 mm   |
| 32SB2114 | 0 – 300 V | 200 W/m | 2 | 3750 Ω/km  | 4.4 mm |
| 32SB3700 | 0 – 300 V | 200 W/m | 2 | 2300 Ω/km  | 4.3 mm |
| 32SB3914 | 0 – 300 V | 200 W/m | 2 | 3000 Ω/km  | 4.1 mm |
| 61SB3150 | 0 – 600 V | 200 W/m | 1 | 500 Ω/km   | 4.3 mm |
| 61SB3200 | 0 – 600 V | 200 W/m | 1 | 660 Ω/km   | 4.6 mm |
| 62SB3700 | 0 – 600 V | 270 W/m | 2 | 2300 Ω/km  | 6.7 mm |
| 62SB3914 | 0 – 600 V | 270 W/m | 2 | 3000 Ω/km  | 5.9 mm |
| 62SP4402 | 0 – 600 V | 270 W/m | 2 | 130 Ω/km   | 7 mm   |
| 32SF2750 | 0 – 300 V | 200 W/m | 2 | 24500 Ω/km | 4 mm   |
| 32SA2600 | 0 – 300 V | 200 W/m | 2 | 19700 Ω/km | 4.1 mm |
| 32SF2900 | 0 – 300 V | 200 W/m | 2 | 29500 Ω/km | 4.1 mm |
| 61SA2130 | 0 – 600 V | 200 W/m | 1 | 4300 Ω/km  | 4.1 mm |
| 61SA2100 | 0 – 600 V | 200 W/m | 1 | 3300 Ω/km  | 4.1 mm |
| 61SA3700 | 0 – 600 V | 200 W/m | 1 | 2300 Ω/km  | 4.1 mm |

|          |           |         |   |            |        |
|----------|-----------|---------|---|------------|--------|
| 32SQ3200 | 0 – 300 V | 200 W/m | 2 | 660 Ω/km   | 4.1 mm |
| 61SA2160 | 0 – 600 V | 200 W/m | 1 | 5250 Ω/km  | 4.1 mm |
| 32SP4458 | 0 – 300 V | 200 W/m | 2 | 150 Ω/km   | 4.8 mm |
| 61SP4467 | 0 – 600 V | 200 W/m | 1 | 155 Ω/km   | 4.3 mm |
| 61SA3850 | 0 – 600 V | 200 W/m | 1 | 2800 Ω/km  | 4.3 mm |
| 61SQ4732 | 0 – 600 V | 200 W/m | 1 | 240 Ω/km   | 4.3 mm |
| 61ST3280 | 0 – 600 V | 200 W/m | 1 | 920 Ω/km   | 4.3 mm |
| 32SA2170 | 0 – 300 V | 200 W/m | 2 | 5600 Ω/km  | 4.2 mm |
| 32SA2200 | 0 – 300 V | 200 W/m | 2 | 6600 Ω/km  | 4.3 mm |
| 32SF1180 | 0 – 300 V | 200 W/m | 2 | 59000 Ω/km | 4.4 mm |
| 32SQ3150 | 0 – 300 V | 200 W/m | 2 | 495 Ω/km   | 4.3 mm |
| 61SA3500 | 0 – 600 V | 200 W/m | 1 | 1640 Ω/km  | 4.3 mm |
| 32SA2318 | 0 – 300 V | 200 W/m | 2 | 10400 Ω/km | 4.4 mm |
| 61SA2200 | 0 – 600 V | 200 W/m | 1 | 6565 Ω/km  | 4.3 mm |
| 61SQ3118 | 0 – 600 V | 200 W/m | 1 | 390 Ω/km   | 4.4 mm |
| 61SQ4581 | 0 – 600 V | 200 W/m | 1 | 190 Ω/km   | 4.4 mm |
| 32SP4734 | 0 – 300 V | 200 W/m | 2 | 240 Ω/km   | 4.4 mm |
| 32SQ3472 | 0 – 300 V | 200 W/m | 2 | 1560 Ω/km  | 4.5 mm |
| 32SQ3293 | 0 – 300 V | 200 W/m | 2 | 965 Ω/km   | 4.5 mm |

|          |           |         |   |            |        |
|----------|-----------|---------|---|------------|--------|
| 32SP4583 | 0 – 300 V | 200 W/m | 2 | 190 Ω/km   | 4.5 mm |
| 32SQ3374 | 0 – 300 V | 200 W/m | 2 | 1240 Ω/km  | 4.6 mm |
| 62SP4561 | 0 – 600 V | 270 W/m | 2 | 185 Ω/km   | 6.7 mm |
| 32SQ3100 | 0 – 300 V | 200 W/m | 2 | 330 Ω/km   | 4.7 mm |
| 62SF1110 | 0 – 600 V | 270 W/m | 2 | 36000 Ω/km | 4.9 mm |
| 62SF2900 | 0 – 600 V | 270 W/m | 2 | 29500 Ω/km | 4.9 mm |
| 62SF2750 | 0 – 600 V | 270 W/m | 2 | 24500 Ω/km | 5.2 mm |
| 62SQ3374 | 0 – 600 V | 270 W/m | 2 | 1240 Ω/km  | 5.5 mm |
| 62ST2115 | 0 – 600 V | 270 W/m | 2 | 3750 Ω/km  | 5.5 mm |
| 62SQ3505 | 0 – 600 V | 270 W/m | 2 | 1670 Ω/km  | 5.5 mm |
| 62SP4775 | 0 – 600 V | 270 W/m | 2 | 255 Ω/km   | 6.4 mm |
| 62SQ3286 | 0 – 600 V | 270 W/m | 2 | 940 Ω/km   | 5.6 mm |
| 62SA2275 | 0 – 600 V | 270 W/m | 2 | 9000 Ω/km  | 5.7 mm |
| 62SF2600 | 0 – 600 V | 270 W/m | 2 | 19700 Ω/km | 5.8 mm |
| 62SQ3150 | 0 – 600 V | 270 W/m | 2 | 495 Ω/km   | 5.8 mm |
| 62SQ3200 | 0 – 600 V | 270 W/m | 2 | 660 Ω/km   | 5.8 mm |
| 62SA2170 | 0 – 600 V | 270 W/m | 2 | 5600 Ω/km  | 6.1 mm |
| 62SA2414 | 0 – 600 V | 270 W/m | 2 | 13600 Ω/km | 6.1 mm |
| 62SF2200 | 0 – 600 V | 270 W/m | 2 | 6600 Ω/km  | 6.2 mm |

|          |           |         |   |           |        |
|----------|-----------|---------|---|-----------|--------|
| 62SQ3100 | 0 – 600 V | 270 W/m | 2 | 330 Ω/km  | 6.5 mm |
| 62ST3505 | 0 – 600 V | 270 W/m | 2 | 1760 Ω/km | 5.5 mm |

## **WARNING**

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at [www.nvent.com](http://www.nvent.com) and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.

### **North America**

Tel +1.800.545.6258  
 Fax +1.800.527.5703  
[thermal.info@nvent.com](mailto:thermal.info@nvent.com)

### **Europe, Middle East, Africa**

Tel +32.16.213.511  
 Fax +32.16.213.604  
[thermal.info@nvent.com](mailto:thermal.info@nvent.com)

### **Asia Pacific**

Tel +86.21.2412.1688  
 Fax +86.21.5426.3167  
[cn.thermal.info@nvent.com](mailto:cn.thermal.info@nvent.com)

### **Latin America**

Tel +1.713.868.4800  
 Fax +1.713.868.2333  
[thermal.info@nvent.com](mailto:thermal.info@nvent.com)

Our powerful portfolio of brands:

**RAYCHEM PYROTENAX TRACER NUHEAT**