

PVT1 PHOTOVOLTAIC SURGE PROTECTION CLASS I+II



CERTIFICATIONS



FEATURES

Uniquely designed for protection of centralized solar inverters on the DC input side and string boxes

Thermal protection included to ensure safe failure modes


Compact, yet high surge rated pluggable design, using minimum DIN rail width

SPECIFICATIONS

Product Attribute	PVT1 Photovoltaic Surge Protection Class I+II, 1,100 V Max Continuous Operating Voltage (Ucpv)	PVT1 Photovoltaic Surge Protection Class I+II, 1,500 VDC Max Continuous Operating Voltage (Ucpv)
Catalog Number	PVT11000R	PVT11500R
Max Continuous Operating Voltage (Ucpv)	1,100 V	1,500 VDC
Nominal Discharge Current (In), IEC	20 kA 8/20 μ s	20 kA 8/20 μ s
Impulse Current (Iimp)	6.25 kA 10/350 μ s	5 kA 10/350 μ s
Total Discharge Current (Itotal)	12.5 kA 10/350 μ s 50.0 kA 8/20 μ s	10 kA 10/350 μ s 40 kA 8/20 μ s
Voltage Protection Level (Up)	4,000 V	5,000 V
Response Time	25 ns Max	25 ns Max
Short Circuit Current Rating (Iscsr)	11 kA	11 kA
Max Continuous Operating Voltage (Vpdc)	1,100 VDC	1,500 VDC
Voltage Protection Rating (VPR)	2,500 V	4,000 V

Product Attribute	PVT1 Photovoltaic Surge Protection Class I+II, 1,100 V Max Continuous Operating Voltage (Ucpv)	PVT1 Photovoltaic Surge Protection Class I+II, 1,500 VDC Max Continuous Operating Voltage (Ucpv)
Nominal Discharge Current (In), UL	20 kA 8/20 μs	20 kA 8/20 μs
Short Circuit Current Rating (SCCR)	50 kA	65 kA
Protection Modes	-ve to PE -ve to +ve +ve to PE	-ve to PE -ve to +ve +ve to PE
Humidity	5 – 95 % RH	5 – 95 % RH
Altitude	2,000 m Max	2,000 m Max
Temperature	-40 to 85 °C	-40 to 85 °C
Mounting	35 mm top hat DIN rail	35 mm top hat DIN rail
Torque(TQ)	4.50 N-m Max	4.50 N-m Max
Enclosure Rating	IP 20	IP 20
Enclosure Material	UL® 94V-0 Thermoplastic	UL® 94V-0 Thermoplastic
Connection, Solid	35 mm ²	35 mm ²
Connection, Flexible	25 mm ²	25 mm ²
Connection, Stranded	35 mm ²	35 mm ²
Remote Contacts	Yes	Yes
Status Indication	Mechanical flag	Mechanical flag
Remote Contact Switching Capacity	1.0 A @ 125 VAC 1.0 A @ 250 VAC 0.5 A @ 12 VDC 0.5 A @ 24 VDC 0.5 A @ 48 VDC	1.0 A @ 125 VAC 1.0 A @ 250 VAC 0.5 A @ 12 VDC 0.5 A @ 24 VDC 0.5 A @ 48 VDC
Depth(D)	85 mm	85 mm
Width(W)	54 mm	54 mm
Height(H)	90 mm	90 mm
Unit Weight	0.460 kg	0.500 kg
Replacement Module	PVT1500M PVT1500SM	PVT1750M PVT1750SM
Certification Details	UL® 1449 Edition 5 Type 1CA	UL® 1449 Edition 5 Type 1CA
Complies With	EN 50539-11 Type 1, Type 2	EN 50539-11 Type 1, Type 2

DIAGRAMS



WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.

North America

+1.800.753.9221

Option 1 – Customer Care

Option 2 – Technical Support

Europe

Netherlands:

+31 800-0200135

France:

+33 800 901 793

Europe

Germany:

800 1890272

Other Countries:

+31 13 5835404

APAC

Shanghai:

+ 86 21 2412 1618/19

Sydney:

+61 2 9751 8500



Our powerful portfolio of brands:
nVent.com CADDY ERICO HOFFMAN RAYCHEM SCHROFF
TRACER