


# LAN Surge Protector

## Power Utilities



### CERTIFICATIONS



### FEATURES

Rugged, metallic enclosure provides both environmental and electrical shielding

Up to CAT6 and POE (Power Over Ethernet) protection in one product


Simple, bi-directional installation

### SPECIFICATIONS

| Catalog Number                        | LANRJ45C6P          |
|---------------------------------------|---------------------|
| Nominal System Voltage (Un)           | 48 VDC              |
| Max Continuous Operating Voltage (Uc) | 50 VDC              |
| Voltage Protection Rating (VPR), L-L  | 150 V               |
| Voltage Protection Rating (VPR), L-PE | 550 V               |
| Nominal Discharge Current (In), L-L   | 150 A 8/20 $\mu$ s  |
| Impulse Current (Iimp)                | 1 kA 10/350 $\mu$ s |

| Catalog Number          | LANRJ45C6P   |
|-------------------------|--------------|
| Rated Load Current (IL) | 1 A          |
| Frequency               | 250 MHz Max  |
| Temperature             | -40 to 80 °C |
| Enclosure Rating        | IP 20        |
| Height (H)              | 75 mm        |
| Width (W)               | 19 mm        |

## DIAGRAMS



## WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at [www.nvent.com](http://www.nvent.com) and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.



Our powerful portfolio of brands:

**CADDY   ERICO   HOFFMAN   ILSCO   SCHROFF   TRACHTE**