We connect and protect

ABS Adjustable Busbar Support Insulator Module

Power Utilities



CERTIFICATIONS

FEATURES

- Modules provide flexibility to select distance between phases and supports
- Extremely robust construction
- Halogen free insulators
- RoHS compliant

SPECIFICATIONS

Table 1/2

Catalog Number	Article Number	Max Working Voltage, IEC (Ui)	Working Temperature	Typical Application Current Rating	Busbars per Phase	Busbar Thickness
ABS1-5MOD	560860	1,000 VAC, 1,500 VDC	-40 to 130 °C	1,700 A Max	1	5 mm

Table 2/2				
Catalog Number	**Article Number**	**Busbar Width**	**Width (W)**	**Unit Weight**
ABS1-5MOD	560860	50 – 125 mm	74 mm	0.640 kg

ADDITIONAL PRODUCT DETAILS

ABS Adjustable Busbar Support High Ampacity Kit available to support up to 200 mm (7.87") busbar width for applications up to 7400 A.

DIAGRAMS





WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.

Our powerful portfolio of brands:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE

©2025 nVent. All nVent marks and logos are owned or licensed by nVent Services GmbH or its affiliates. All other trademarks are the property of their respective owners. nVent reserves the right to change specifications without notice.

This document is system-generated.