


MI Series Inconel 600 HIQ Heating Cable



nVent RAYCHEM HIQ Inconel 600 sheathed mineral insulated (MI) series resistance trace heating cables provide freeze protection and process temperature maintenance. They can be used for exposure temperatures up to 700 °C (joint dependent) and typical power outputs up to 300 W/m. Alloy 600 sheath offers excellent corrosion resistance to a wide range of organic acids, alkalis and chloride stress-corrosion cracking. Approved for use in hazardous areas. Available 'fast track' as configured heating units.

FEATURES

Reduced total installed cost

Reduced power supply costs: lower start up currents compared with other technologies

Simple controls: current monitoring on series resistance provides instant visibility on critical circuits

Fast track/expressed service for configured heating units for eligible designs

Standard 550 °C continuous withstand temperature, with braze weld technology

Optional 700 °C continuous withstand temperature, with laser welded technology

Excellent corrosion resistance to a wide range of organic acids, alkalis and chloride stress-corrosion cracking

SPECIFICATIONS

| | |
|--|--------------------------|
| Min Cable Spacing: | 25 mm |
| Max Power Output: | 300 W/m |
| Max Continuous Exposure Temperature, Power Off: | 680 °C |
| Min Installation Temperature: | -60 °C |
| Supply Voltage: | 0 – 500 V |
| Area Classification: | Non-Hazardous; Hazardous |
| Sheath Material: | Inconel 600 |
| Insulation Material: | Magnesium Oxide |

Table 1/1

| Catalog Number | Nominal Resistance @ 20°C | Outer Diameter |
|----------------|---------------------------|----------------|
| HIQ1M10K | 10000 Ω/km | 3.2 mm |

| Catalog Number | Nominal Resistance @ 20°C | Outer Diameter |
|----------------|---------------------------|----------------|
| HIQ1M4000 | 4000 Ω/km | 3.2 mm |
| HIQ1M6300 | 6300 Ω/km | 3.2 mm |
| HIQ1M2500 | 2500 Ω/km | 3.4 mm |
| HIQ1M1600 | 1600 Ω/km | 3.6 mm |
| HIQ1M1000 | 1000 Ω/km | 3.9 mm |
| HIQ1M160 | 160 Ω/km | 6.5 mm |
| HIQ1M630 | 630 Ω/km | 4.3 mm |
| HIQ1M400 | 400 Ω/km | 4.7 mm |
| HIQ1M250 | 250 Ω/km | 5.3 mm |

WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.

North America

Tel +1.800.545.6258
 Fax +1.800.527.5703
thermal.info@nvent.com

Europe, Middle East, Africa

Tel +32.16.213.511
 Fax +32.16.213.604
thermal.info@nvent.com

Asia Pacific

Tel +86.21.2412.1688
 Fax +86.21.5426.3167
cn.thermal.info@nvent.com

Latin America

Tel +1.713.868.4800
 Fax +1.713.868.2333
thermal.info@nvent.com

Our powerful portfolio of brands:

RAYCHEM PYROTENAX TRACER NUHEAT