



# Copper Ground Plate



The nVent ERICO Copper Ground Plate is designed to create an equipotential plane and help protect personnel and valuable equipment. These plates offer mechanical attachment points for grounding, providing a distinct solution for various applications.

## DIAGRAMS



## FEATURES

Provides a large surface area to dissipate current into the ground

Available in a variety of sizes and pigtail configurations

## SPECIFICATIONS

**Material:** Copper

Table 1/2

| Catalog Number      | Finish | Width  | Length | Pigtail Connection | Pigtail Length | Conductor Size |
|---------------------|--------|--------|--------|--------------------|----------------|----------------|
| GPECNHM096          | Bare   | 914 mm | 2438mm | None               |                |                |
| GPECCAM036          | Bare   | 914 mm | 914mm  | None               |                |                |
| GPECEAJ0241<br>G024 | Bare   | 457 mm | 610mm  | End                | 610mm          | #6 Solid       |

| CatalogNumber       | Finish | Width  | Length | Pigtail Connection | Pigtail Length | Conductor Size |
|---------------------|--------|--------|--------|--------------------|----------------|----------------|
| GPECEAK0241<br>G024 | Bare   | 610 mm | 610mm  | End                | 610mm          | #6 Solid       |
| GPECEAK0241<br>H024 | Bare   | 610 mm | 610mm  | End                | 610mm          | #6 Stranded    |
| GPECNAJ018          | Bare   | 457 mm | 457mm  | None               |                |                |
| GPECNAK024          | Bare   | 610 mm | 610mm  | None               |                |                |
| GPECCBJ0181T<br>060 | Bare   | 457 mm | 457mm  | Continuous         | 1524mm         | #2 Solid       |
| GPECEBH0121<br>V024 | Bare   | 305 mm | 305mm  | End                | 610mm          | #2 Stranded    |
| GPECEBH0241<br>K024 | Bare   | 305 mm | 610mm  | End                | 610mm          | #4 Solid       |
| GPECEBQ0171<br>G120 | Bare   | 432 mm | 432mm  | End                | 3048mm         | #6 Solid       |
| GPECNBH012          | Bare   | 305 mm | 305mm  | None               |                |                |
| GPECNBH024          | Bare   | 305 mm | 610mm  | None               |                |                |
| GPECCDK0241<br>L024 | Bare   | 610 mm | 610mm  | Continuous         | 610mm          | #4 Stranded    |
| GPECCDM0361<br>T10T | Tinned | 914 mm | 914mm  | Continuous         | 254mm          | #2 Solid       |
| GPECEDK0241L<br>024 | Bare   | 610 mm | 610mm  | End                | 610mm          | #4 Stranded    |
| GPECEDK0242<br>Q036 | Bare   | 610 mm | 610mm  | End                | 914mm          | 4/0 Stranded   |

| CatalogNumber       | Finish | Width  | Length | Pigtail Connection | Pigtail Length | Conductor Size |
|---------------------|--------|--------|--------|--------------------|----------------|----------------|
| GPECNDF006          | Bare   | 152 mm | 152mm  | None               |                |                |
| GPECNDH024          | Bare   | 305 mm | 610mm  | None               |                |                |
| GPECNDK024T         | Tinned | 610 mm | 610mm  | None               |                |                |
| GPECNDM036T         | Tinned | 914 mm | 914mm  | None               |                |                |
| GPECCEK0242<br>C036 | Bare   | 610 mm | 610mm  | Continuous         | 914mm          | 1/0 Stranded   |
| GPECEEK0241T<br>024 | Bare   | 610 mm | 610mm  | End                | 610mm          | #2 Solid       |
| GPECEEK0242<br>Q008 | Bare   | 610 mm | 610mm  | End                | 203mm          | 4/0 Stranded   |
| GPECEEK0242<br>Q060 | Bare   | 610 mm | 610mm  | End                | 1524mm         | 4/0 Stranded   |
| GPECEEK0242<br>Q120 | Bare   | 610 mm | 610mm  | End                | 3048mm         | 4/0 Stranded   |
| GPECEEK0242<br>Q180 | Bare   | 610 mm | 610mm  | End                | 4572mm         | 4/0 Stranded   |
| GPECEEK0361T<br>024 | Bare   | 610 mm | 914mm  | End                | 610mm          | #2 Solid       |
| GPECNEB024          | Bare   | 51 mm  | 610mm  | None               |                |                |
| GPECNED004          | Bare   | 102 mm | 102mm  | None               |                |                |
| GPECNED012          | Bare   | 102 mm | 305mm  | None               |                |                |
| GPECNED014          | Bare   | 102 mm | 356mm  | None               |                |                |
| GPECNED096          | Bare   | 102 mm | 2438mm | None               |                |                |

| CatalogNumber | Finish | Width  | Length | Pigtail Connection | Pigtail Length | Conductor Size |
|---------------|--------|--------|--------|--------------------|----------------|----------------|
| GPECNEG024    | Bare   | 229 mm | 610mm  | None               |                |                |
| GPECNEH016    | Bare   | 305 mm | 406mm  | None               |                |                |
| GPECNEK024    | Bare   | 610 mm | 610mm  | None               |                |                |
| GPECNEM040    | Bare   | 914 mm | 1016mm | None               |                |                |
| GPECNFH033    | Bare   | 305 mm | 838mm  | None               |                |                |
| GPECNFK024    | Bare   | 610 mm | 610mm  | None               |                |                |
| GPECNGF012    | Bare   | 152 mm | 305mm  | None               |                |                |
| GPECNGK024    | Bare   | 610 mm | 610mm  | None               |                |                |

Table 2/2

| Catalog Number  | Thickness |
|-----------------|-----------|
| GPECNHM096      | 0.4 mm    |
| GPECCAM036      | 0.79 mm   |
| GPECEAJ0241G024 | 0.79 mm   |
| GPECEAK0241G024 | 0.79 mm   |
| GPECEAK0241H024 | 0.79 mm   |
| GPECNAJ018      | 0.79 mm   |
| GPECNAK024      | 0.79 mm   |
| GPECCBJ0181T060 | 1.59 mm   |
| GPECEBH0121V024 | 1.59 mm   |

| Catalog Number  | Thickness |
|-----------------|-----------|
| GPECEBH0241K024 | 1.59 mm   |
| GPECEBQ0171G120 | 1.59 mm   |
| GPECNBH012      | 1.59 mm   |
| GPECNBH024      | 1.59 mm   |
| GPECCDK0241L024 | 3.18 mm   |
| GPECCDM0361T10T | 3.18 mm   |
| GPECEDK0241L024 | 3.18 mm   |
| GPECEDK0242Q036 | 3.18 mm   |
| GPECNDF006      | 3.18 mm   |
| GPECNDH024      | 3.18 mm   |
| GPECNDK024T     | 3.18 mm   |
| GPECNDM036T     | 3.18 mm   |
| GPECCEK0242C036 | 6.35 mm   |
| GPECEEK0241T024 | 6.35 mm   |
| GPECEEK0242Q008 | 6.35 mm   |
| GPECEEK0242Q060 | 6.35 mm   |
| GPECEEK0242Q120 | 6.35 mm   |
| GPECEEK0242Q180 | 6.35 mm   |

| Catalog Number  | Thickness |
|-----------------|-----------|
| GPECEEK0361T024 | 6.35 mm   |
| GPECNEB024      | 6.35 mm   |
| GPECNED004      | 6.35 mm   |
| GPECNED012      | 6.35 mm   |
| GPECNED014      | 6.35 mm   |
| GPECNED096      | 6.35 mm   |
| GPECNEG024      | 6.35 mm   |
| GPECNEH016      | 6.35 mm   |
| GPECNEK024      | 6.35 mm   |
| GPECNEM040      | 6.35 mm   |
| GPECNFH033      | 9.53 mm   |
| GPECNFK024      | 9.53 mm   |
| GPECNGF012      | 12.7 mm   |
| GPECNGK024      | 12.7 mm   |

| GPE-C-E-A-H-024-1L-024-(T) |                                                |                                                                                                                                                                                      |
|----------------------------|------------------------------------------------|--------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|
| GPE                        | Ground Plate Electrode                         |                                                                                                                                                                                      |
| C                          | Material                                       | C: Copper (C11000)                                                                                                                                                                   |
| E                          | Pigtail Connection                             | C: Continuous (2 x "L J" ERICO CADWELD Connection)<br>E: End ("L J" ERICO CADWELD Connection Style)<br>N: No Pigtail                                                                 |
| A                          | Plate Thickness Code (Stock Tolerance)         | A: 1/32" (Min. for Lightning – Cu)<br>B: 1/16" (Min. for Power – Cu)<br>C: 3/32"<br>D: 1/8"<br>E: 1/4" (Min. for Power – Stl.)<br>F: 3/8"<br>G: 1/2"<br>H: 1/64" (26 GA)<br>J: 3/16" |
| H                          | Plate Width Code                               | A: 1" · B: 2" · C: 3" · D: 4" · E: 5" · F: 6" · G: 9" · H: 12" · J: 18"<br>K: 24" · L: 30" · M: 36" · N: 42" · P: 48" · Q: 17" · R: 10"                                              |
| 024                        | Plate Length Code (inches) (3 digits required) |                                                                                                                                                                                      |
| 1L*                        | Pigtail Cable Type (ERICO Cable Code)          |                                                                                                                                                                                      |
| 024*                       | Pigtail Length (inches)                        |                                                                                                                                                                                      |
| (T)*                       | Tinned                                         |                                                                                                                                                                                      |

\* Empty if none

## WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at [www.nvent.com](http://www.nvent.com) and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.

 **WARNING:** This product can expose you to chemicals including lead, which is known to the State of California to cause cancer and birth defects or other reproductive harm. For more information go to [www.P65Warnings.ca.gov](http://www.P65Warnings.ca.gov).

### North America

+1.800.753.9221

Option 1 – Customer Care

Option 2 – Technical

Support

### Europe

Netherlands:

+31 800-0200135

France:

+33 800 901 793

### Europe

Germany:

800 1890272

Other Countries:

+31 13 5835404

### APAC

Shanghai:

+ 86 21 2412 1618/19

Sydney:

+61 2 9751 8500



Our powerful portfolio of brands:

**CADDY**

**ERICO**

**HOFFMAN**

**ILSCO**

**SCHROFF**

**TRACHTE**