

nVent CADDY Swift Clip Strut Clamp for Tube/Pipe



FEATURES

Secures pipe while allowing it to expand, preventing cracked and fractured joints

Snap-in and twist installation requires no tools

Fits directly into vertical and horizontal strut channels

Use for installation of refrigeration, A/C tubing and PEX piping in horizontal and vertical channels

Compliant with UL® 2043 and suitable for use in air handling (plenum) spaces

SPECIFICATIONS

Material: Polyamide
Working Temperature: -40 to 140 °C

Table 1/1

Catalog Number	Outer Diameter (OD)	Copper Tube Size	NB/DN	Width (W)
TSM0037	10 mm	1/4"		41 mm
TSM0050	12 mm	3/8"		41 mm
TSM0062	16 mm	1/2"		41 mm
TSM0087	22 mm	3/4"	15	41 mm


Catalog Number	Outer Diameter (OD)	Copper Tube Size	NB/DN	Width (W)
TSM0075	20 mm	5/8"		41 mm
TSM0112	28 mm	1"		41 mm
TSM0137	35 mm	1 1/4"		41 mm
TSM0162	41 mm	1 1/2"		41 mm

ADDITIONAL PRODUCT DETAILS

Can also be used with PEX piping. For PEX pipe sizes, refer to the Copper Tube Size column.

Clip must be installed with temperature at or above 14 °F (-10 °C).

DIAGRAMS



WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.

North America

+1.800.753.9221

Option 1 – Customer Care

Option 2 – Technical

Support

Europe

Netherlands:

+31 800-0200135

France:

+33 800 901 793

Europe

Germany:

800 1890272

Other Countries:

+31 13 5835404

APAC

Shanghai:

+ 86 21 2412 1618/19

Sydney:

+61 2 9751 8500



Our powerful portfolio of brands:

CADDY

ERICO

HOFFMAN

ILSCO

SCHROFF

TRACHTE

