

401 Clevis Hanger



CERTIFICATIONS



FEATURES

Recommended for the suspension of stationary non-insulated pipe lines

Flared edges help prevent sharp surfaces from coming into contact with the pipe (1/2" to 2" pipe sizes)

Clevis bottom pivots to allow pipe to be fed from either direction

Conforms with Federal Specification WW-H-171 (Type 1), Manufacturers Standardization Society (MSS) SP-58 (Type 1)

SPECIFICATIONS

Material: Steel

Table 1/2

Catalog Number	Finish	NB/DN	Outer Diameter (OD)	Rod Size (RS)	A	B
4010050EG	Electrogalvanized, Pregalvanized	15	21 mm	M10	59 mm	29 mm
4010075EG	Electrogalvanized, Pregalvanized	20	27 mm	M10	64 mm	32 mm

CatalogNumber	Finish	NB/DN	Outer Diameter (OD)	Rod Size (RS)	A	B
4010100EG	Electrogalvanized, Pregalvanized	25	34 mm	M10	71 mm	35 mm
4010125EG	Electrogalvanized, Pregalvanized	32	43 mm	M10	80 mm	40 mm
4010150EG	Electrogalvanized, Pregalvanized	40	48 mm	M10	94 mm	53 mm
4010200EG	Electrogalvanized, Pregalvanized	50	60 mm	M10	110 mm	63 mm
4010250EG	Electrogalvanized, Pregalvanized	65	76 mm	M12	134 mm	78 mm
4010250HD	Hot-Dip Galvanized		73 mm		133.35 mm	71.44 mm
4010300EG	Electrogalvanized, Pregalvanized	80	89 mm	M12	154 mm	90 mm
4010300HD	Hot-Dip Galvanized		88.9 mm		152.4 mm	82.55 mm
4010350EG	Electrogalvanized, Pregalvanized	90	101.6 mm	M12	172 mm	101 mm
4010400EG	Electrogalvanized, Pregalvanized	100	114 mm	M16	189 mm	111 mm
4010400HD	Hot-Dip Galvanized		114.3 mm		196.85 mm	107.95 mm
4010500EG	Electrogalvanized, Pregalvanized	125	140 mm	M16	231 mm	130 mm
4010600EG	Electrogalvanized, Pregalvanized	150	165 mm	M20	268 mm	153 mm
4010800EG	Electrogalvanized, Pregalvanized	200	219 mm	M20	356 mm	204 mm
4011000EG	Electrogalvanized, Pregalvanized	250	273 mm	M20	419 mm	230 mm


CatalogNumber	Finish	NB/DN	Outer Diameter (OD)	Rod Size (RS)	A	B
4011200EG	Electrogalvanized, Pregalvanized	300	324 mm	M20	473 mm	258 mm
4011400EG	Electrogalvanized, Pregalvanized	350	356 mm	M24	552 mm	311 mm
4011600EG	Electrogalvanized, Pregalvanized	400	406 mm	M24	609 mm	342.8 mm
4011800EG	Electrogalvanized, Pregalvanized	450	457 mm	M28	680 mm	380.6 mm
4012000EG	Electrogalvanized, Pregalvanized	500	508 mm	M32	762 mm	432.3 mm

Table 2/2

Catalog Number	C	Static Load	Certifications
4010050EG	9 mm	2700N	UL, cUL, ITB
4010075EG	9 mm	2700N	UL, cUL, ITB
4010100EG	9 mm	2700N	UL, cUL, ITB
4010125EG	9 mm	2700N	UL, cUL, ITB
4010150EG	17 mm	2700N	UL, cUL, ITB
4010200EG	22 mm	2700N	UL, cUL, ITB
4010250EG	25 mm	5000N	UL, cUL, ITB
4010250HD	26.99 mm	5000N	UL, cUL
4010300EG	29 mm	5000N	UL, cUL, ITB
4010300HD	22.23 mm	5000N	UL, cUL

Catalog Number	C	Static Load	Certifications
4010350EG	34 mm	5000N	UL, cUL
4010400EG	35 mm	5000N	UL, cUL, ITB
4010400HD	44.45 mm	5000N	UL, cUL
4010500EG	41 mm	6400N	UL, cUL, ITB
4010600EG	48 mm	8600N	UL, cUL, ITB
4010800EG	80 mm	8900N	UL, cUL, ITB
4011000EG	66 mm	16000N	ITB
4011200EG	78 mm	17000N	ITB
4011400EG	111.4 mm	18700N	ITB
4011600EG	117.8 mm	20500N	ITB
4011800EG	130.8 mm	21400N	ITB
4012000EG	162.8 mm	21400N	ITB

DIAGRAMS



WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause

product malfunction, property damage, serious bodily injury and death and/or void your warranty.

North America

+1.800.753.9221
Option 1 – Customer Care
Option 2 – Technical
Support

Europe

Netherlands:
+31 800-0200135
France:
+33 800 901 793

Europe

Germany:
800 1890272
Other Countries:
+31 13 5835404

APAC

Shanghai:
+ 86 21 2412 1618/19
Sydney:
+61 2 9751 8500



Our powerful portfolio of brands:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE

