

H-MSM Conduit/Pipe to Flange Clip, Side Mount



CERTIFICATIONS



FEATURES

Supports conduit/pipe or cable from beam flanges

Snap close clip pivots a full 360°

Requires only a hammer to install

SPECIFICATIONS

Finish: nVent CADDY Armour


Material: Spring Steel

Table 1/1

Catalog Number	Outer Diameter (OD)	Flange Thickness (FT)	Static Load	Certifications
16M24SM	23.4 - 35 mm	3 - 8 mm	120N	UL, cUL
20M24SM	35 - 42 mm	3 - 8 mm	120N	cUL, UL
24M24SM	42 - 50 mm	3 - 8 mm	120N	cUL, UL

Catalog Number	Outer Diameter (OD)	Flange Thickness (FT)	Static Load	Certifications
32M24SM	50 - 60 mm	3 - 8 mm	120N	UL, cUL
6M24SM	14 - 18 mm	3 - 8 mm	120N	UL, cUL
812M24SM	18 - 30 mm	3 - 8 mm	120N	UL, cUL, ITB
16M58SM	23.4 - 35 mm	8 - 14 mm	120N	UL, cUL
20M58SM	35 - 42 mm	8 - 14 mm	120N	
24M58SM	42 - 50 mm	8 - 14 mm	120N	cUL, UL
32M58SM	50 - 60 mm	8 - 14 mm	120N	UL, cUL
6M58SM	14 - 18 mm	8 - 14 mm	120N	UL, cUL
812M58SM	18 - 30 mm	8 - 14 mm	120N	cUL, ITB, UL
6M912SM	14 - 18 mm	14 - 20 mm	120N	
812M912SM	18 - 30 mm	14 - 20 mm	120N	UL, cUL, ITB
16M912SM	23.4 - 35 mm	14 - 20 mm	120N	cUL, UL
20M912SM	35 - 42 mm	14 - 20 mm	120N	
24M912SM	42 - 50 mm	14 - 20 mm	120N	cUL, UL
32M912SM	50 - 60 mm	14 - 20 mm	120N	cUL, UL

DIAGRAMS



WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.

North America

+1.800.753.9221
Option 1 – Customer Care
Option 2 – Technical
Support

Europe

Netherlands:
+31 800-0200135
France:
+33 800 901 793

Europe

Germany:
800 1890272
Other Countries:
+31 13 5835404

APAC

Shanghai:
+ 86 21 2412 1618/19
Sydney:
+61 2 9751 8500



Our powerful portfolio of brands:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE

