

# nVent CADDY Pyramid H-Frame Post Base



## FEATURES

Foam or rubber bottom offers low abrasion interface for better roof membrane protection

Compatible with roof surfaces including single ply, bituminous, metal and spray foam

Provides superior load distribution, even with varying rooftop surfaces

Rubber rooftop interface ideal for solar panel array installations

Mounting hardware pre-installed in bases

Hot-dip galvanized and UV stabilized for long lasting performance

Accepts standard strut channels

## SPECIFICATIONS

<b>Static Load Safety Factor:</b>	3:1
<b>Finish:</b>	Hot-Dip Galvanized
<b>Material:</b>	Steel;Polypropylene;Polyethylene
<b>Temperature:</b>	-34 to 54.4 °C


Table 1/2

Catalog Number	Rooftop Interface	Strut Type	Height (H)	Length (L)	Width (W)	Surface Area
PHB	Foam	A (41 x 41 mm)	117 mm	314mm	314 mm	0.09m <sup>2</sup>
PHBR	Rubber	A (41 x 41 mm)	118 mm	314mm	314 mm	0.1m <sup>2</sup>

Table 2/2

Catalog Number	Unit Weight	Static Load
PHB	1.8 kg	3335N
PHBR	2 kg	3335N

## DIAGRAMS



## WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at [www.nvent.com](http://www.nvent.com) and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.

### North America

+1.800.753.9221  
Option 1 – Customer Care  
Option 2 – Technical  
Support

### Europe

Netherlands:  
+31 800-0200135  
France:  
+33 800 901 793

### Europe

Germany:  
800 1890272  
Other Countries:  
+31 13 5835404

### APAC

Shanghai:  
+ 86 21 2412 1618/19  
Sydney:  
+61 2 9751 8500



Our powerful portfolio of brands:

**CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE**

