

nVent CADDY Stainless Steel Manual Swaging Tool



The nVent CADDY Stainless Steel Manual Swaging Tool is a simple yet effective solution to crimp stainless steel nVent CADDY Oval Sleeves onto size 3/16 stainless steel cable. Designed to be used on rooftop job sites or in the shop, crimping stainless steel sleeves with nVent CADDY Pyramid Rooftop Cable Bracing kits quickly and easily. Create a secure connection with our start-to-finish rooftop offering and easily secure a variety of rooftop equipment such as metal duct, HVAC units, piping and walkways. By utilizing the Stainless Steel Manual Swaging Tool, contractors can have confidence that splices are secure and reliable.

FEATURES

Designed to be used exclusively with size #36 nVent CADDY Stainless Steel Oval Sleeves and size 3/16 stainless steel nVent CADDY Pyramid Rooftop Anchor Cable Bracing

Versatile solution made for both on-site and in-shop use

Helps brace and lock oval sleeves into place on metal cable to create a fixed bond

SPECIFICATIONS

Table 1/1

Catalog Number	Brace Size	Material
CSB36SBSS	#12, #18, #36	Steel

WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.

North America

+1.800.753.9221

Option 1 – Customer Care

Option 2 – Technical

Support

Europe

Netherlands:

+31 800-0200135

France:

+33 800 901 793

Europe

Germany:

800 1890272

Other Countries:

+31 13 5835404

APAC

Shanghai:

+ 86 21 2412 1618/19

Sydney:

+61 2 9751 8500



Our powerful portfolio of brands:

CADDY

ERICO

HOFFMAN

ILSCO

SCHROFF

TRACHTE

