

WinterGard Self-Regulating Heating Cable, TruckPak



nVent RAYCHEM WinterGard self-regulating trace heating cables provide energy efficient and easy to use solutions for pipe freeze protection. This TruckPak kit includes heating cable, two H900 hardwired power/end seal kits, one H910 splice/tee kit, and one H903 application tape. Available as 120 V, 100 ft, 3W/ft or 6W/ft.

FEATURES

Energy efficient and safe: self regulating cable, advanced energy saving controls, no overheating possible

SPECIFICATIONS

Nominal Height:	4.57 mm
Nominal Width:	9.65 mm
Max Continuous Exposure Temperature, Power On:	65 °C
Ground Path Type:	Braid
Outer Jacket Material:	None

Table 1/1

Catalog Number	Item Name	Nominal Voltage
945417-000	H621-100	240 V
192789-000	H611-100	120 V
144941-000	H311-100	120 V

WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause

product malfunction, property damage, serious bodily injury and death and/or void your warranty.

North America

Tel +1.800.545.6258

Fax +1.800.527.5703

thermal.info@nvent.com

**Europe, Middle East,
Africa**

Tel +32.16.213.511

Fax +32.16.213.604

thermal.info@nvent.com

Asia Pacific

Tel +86.21.2412.1688

Fax +86.21.5426.3167

cn.thermal.info@nvent.com

Latin America

Tel +1.713.868.4800

Fax +1.713.868.2333

thermal.info@nvent.com

Our powerful portfolio of brands:

RAYCHEM PYROTENAX TRACER NUHEAT