


# nVent CADDY Rod Lock Bottom-Mount Duct Bracket



## CERTIFICATIONS



## FEATURES

Ideal for modular assembly – allows attachment of brackets to sections of duct while safely on the ground

Slotted holes in bracket allow for horizontal adjustment of the bracket relative to the duct

Easy "push-to-install" design allows installers to simply push the threaded rod through the mounting hole, instantly holding it in position

Ready to use out of the box and eliminates the need for cutting and preparing sections of strut, angle iron, or strap

Integrated adjustment nut enables fine tuning the system height up or down

Lock nut can be finger tightened, locking the rod in place

Extremely useful in tight spaces where wrenches are difficult to use

Includes self-tapping sheet metal screws to attach bracket to duct

## SPECIFICATIONS


Table 1/2

| Catalog Number | Material | Finish | Rod Size (RS) | Height (H) | Length (L) | Width (W) |
|----------------|----------|--------|---------------|------------|------------|-----------|
|----------------|----------|--------|---------------|------------|------------|-----------|

|           |       |                   |       |          |        |          |
|-----------|-------|-------------------|-------|----------|--------|----------|
| CRLD37BEG | Steel | Electrogalvanized | 0.375 | 43.18 mm | 88.9mm | 101.6 mm |
|-----------|-------|-------------------|-------|----------|--------|----------|

| Table 2/2      |         |             |
|----------------|---------|-------------|
| Catalog Number | A       | Static Load |
| CRLD37BEG      | 63.5 mm | 2890N       |

### DIAGRAMS



### WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at [www.nvent.com](http://www.nvent.com) and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.

#### North America

+1.800.753.9221  
Option 1 – Customer Care  
Option 2 – Technical  
Support

#### Europe

Netherlands:  
+31 800-0200135  
France:  
+33 800 901 793

#### Europe

Germany:  
800 1890272  
Other Countries:  
+31 13 5835404

#### APAC

Shanghai:  
+ 86 21 2412 1618/19  
Sydney:  
+61 2 9751 8500



Our powerful portfolio of brands:

CADDY   ERICO   HOFFMAN   ILSCO   SCHROFF   TRACHTE

