

SIMPLIFY AND SPEED UP INSTALLATION WITH MI CABLE FACTORY PRE-TERMINATED ENDS




nVent PYROTENAX is the world leader in the production of Mineral Insulated (MI) cables for various applications such as protecting critical circuits, general purpose wiring for space savings installations, outdoor and direct burial installations, and so much more. Due to its unique properties, nVent PYROTENAX MI cables do not require additional physical protection. The contractor can realize significant material and labor cost savings since additional conduit, boxes, and associated accessories aren't required.

Now, contractors can realize even GREATER cost savings in the field with the introduction of nVent PYROTENAX **Factory Installed Pre-Terminated Ends**. Whether single conductor, multi conductor, or twisted pair MI cables, factory installed Pre-Terminated Ends is a great way to minimize cost uncertainty in the field. No more guessing or incorrectly estimating the time needed to complete a termination. Pre-Terminated Ends limits your exposure to ever changing job conditions and help maximize profits.



Pre-Terminated Ends for single conductors come in several options and configurations, including:

- Cable ends stripped, meggered, and sealed
- Cable ends stripped, meggered, sealed, with a connector crimped on to the MI conductor (stranded wire attached by contractor)
- Cable ends stripped, meggered, sealed, with a stranded tail crimped on (termination is complete and ready for final connection to equipment)




Completed MI cable termination - inside view

For Multi-conductor cables, the cables are supplied with ends stripped, meggered, sealed with stranded tails brazed on (termination is complete and ready for final connection to equipment).

All options come with the brass entry gland that threads directly into the brass entry plate (for single conductor cables) or attaches directly to the box/equipment via a double locknut (for multi-conductor cables) for a reliable and sustainable method of attachment.

For further information and to determine which option is best for your particular project, please contact your local nVent PYROTENAX Sales Representative.



Pre-terminated 4/0 MI cable sized-up to 500 kcmil THHN tail



Pre-terminated 6/3 multi conductor MI cable



Completed MI cable terminations

North America

Tel: +1.800.545.6258
Fax: +1.800.527.5703
thermal.info@nVent.com

Europe, Middle East, Africa

Tel: +32.16.213.511
Fax: +32.16.213.604
thermal.info@nVent.com

Asia Pacific

Tel: +86.21.2412.1688
Fax: +86.21.5426.3167
cn.thermal.info@nVent.com

Latin America

Tel: +1.713.868.4800
Fax: +1.713.868.2333
thermal.info@nVent.com



Our powerful portfolio of brands:

nVent.com/PYROTENAX

CADDY

ERICO

HOFFMAN

RAYCHEM

SCHROFF

TRACER

© 2020 nVent. All nVent marks and logos are owned or licensed by nVent Services GmbH or its affiliates. All other trademarks are the property of their respective owners. nVent reserves the right to change specifications without notice.

PYROTENAX-FLY-H60859-FactoryPreTermProgram-EN-2003