

Frostex Self-Regulating Heating Cable



nVent RAYCHEM Frostex self-regulating trace heating cables provide pipe freeze protection for residential applications. Each heating cable circuit requires a Frostex 9800 FlexFit plug kit.

FEATURES

Simple to design

Easy to install

Reliable during long life: 2 year product warranty available, maintenance free

SPECIFICATIONS

Nominal Thickness:	3.8 mm
Nominal Width:	6.4 mm
Nominal Power Output @ 10°C, 120V:	10 W/m
Nominal Cable Weight:	60 g/m
Nominal Voltage:	120 V
Min Installation Temperature:	-18 °C
Ground Path Type:	Braid
Color:	Clear
Outer Jacket Material:	None

Table 1/1

Catalog Number	Item Name	Length
702549-000	FROSTEX-2250	75 m
777445-000	FROSTEX-2102	30 m
628393-000	FROSTEX-2502	150 m

WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.

North America

Tel +1.800.545.6258

Fax +1.800.527.5703

thermal.info@nvent.com

Europe, Middle East, Africa

Tel +32.16.213.511

Fax +32.16.213.604

thermal.info@nvent.com

Asia Pacific

Tel +86.21.2412.1688

Fax +86.21.5426.3167

cn.thermal.info@nvent.com

Latin America

Tel +1.713.868.4800

Fax +1.713.868.2333

thermal.info@nvent.com

Our powerful portfolio of brands:

RAYCHEM PYROTENAX TRACER NUHEAT