

# HTV Self-Regulating Heating Cable



nVent RAYCHEM HTV self-regulating heating cable is designed for freeze protection or process temperature maintenance of pipes and vessels up to 205°C continuously, with a maximum exposure temperature of 260°C. The HTV cable has a solid construction with a high power retention (HPR) heating core and pressure extruded electrical insulation. It is then integrated with a robust metallic braid and a chemically resistant fluoropolymer outer jacket.

## FEATURES

High power retention (HPR) heating core

Power retention: At least 95% after 10 years

Design life: 30 years or more depending on application

Simplified design in hazardous area: T3 and T2

Longer circuit lengths due to larger cross section conductors

Fast installation: cut-to-length, multiple overlaps allowed, meter markings, user-friendly connections kits

Safe and efficient in operation: no overheating, uniform pipe temperatures, energy saving technology

Reliable during long life: 10 year product warranty available, maintenance free

## SPECIFICATIONS

<b>Max Maintain or Continuous Exposure Temperature, Power On:</b>	205 °C
<b>Max Intermittent Exposure Temperature, Power On/Off:</b>	260 °C
<b>Max Cumulative Hours for Intermittent Exposure:</b>	2000 h
<b>Ground Path Type:</b>	Braid
<b>Area Classification:</b>	Non-Hazardous; Hazardous
<b>Outer Jacket Material:</b>	High Temperature Fluoropolymer

Table 1/1

Catalog Number	Item Name	Supply Voltage	Nominal Power Output @ 10°C, 230V	Nominal Power Output @ 10°C, 120V
P000004312	3HTV1-CT	90 – 130 V		9 W/m

Catalog Number	Item Name	Supply Voltage	Nominal Power Output @ 10°C, 230V	Nominal Power Output @ 10°C, 120V
P000004313	5HTV1-CT	90 – 130 V		16 W/m
P000004314	8HTV1-CT	90 – 130 V		28 W/m
P000004315	10HTV1-CT	90 – 130 V		32 W/m
P000004316	12HTV1-CT	90 – 130 V		39 W/m
P000004317	15HTV1-CT	90 – 130 V		49 W/m
P000004318	20HTV1-CT	90 – 130 V		65 W/m
P000004319	3HTV2-CT	190 – 277 V	9 W/m	
P000004320	5HTV2-CT	190 – 277 V	16 W/m	
P000004321	8HTV2-CT	190 – 277 V	25 W/m	
P000004322	10HTV2-CT	190 – 277 V	32 W/m	
P000004323	12HTV2-CT	190 – 277 V	38 W/m	
P000004324	15HTV2-CT	190 – 277 V	48 W/m	
P000004325	20HTV2-CT	190 – 277 V	64 W/m	
2000003152	28HTV2-CT	190 – 277 V	90 W/m	

## WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at [www.nvent.com](http://www.nvent.com) and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.

**North America**

Tel +1.800.545.6258

Fax +1.800.527.5703

[thermal.info@nvent.com](mailto:thermal.info@nvent.com)

**Europe, Middle East,  
Africa**

Tel +32.16.213.511

Fax +32.16.213.604

[thermal.info@nvent.com](mailto:thermal.info@nvent.com)

**Asia Pacific**

Tel +86.21.2412.1688

Fax +86.21.5426.3167

[cn.thermal.info@nvent.com](mailto:cn.thermal.info@nvent.com)

**Latin America**

Tel +1.713.868.4800

Fax +1.713.868.2333

[thermal.info@nvent.com](mailto:thermal.info@nvent.com)

Our powerful portfolio of brands:

**RAYCHEM   PYROTENAX   TRACER   NUHEAT**