

# Thermoelectric Coolers Indoor/Outdoor



Thermoelectric Coolers minimize downtime and component loss by removing heat around critical components within an enclosure. These compact, low-profile coolers using the Peltier effect allow for cooling of small indoor and outdoor enclosures. No condensers, compressors or filters are required making it a reliable solution for demanding low-maintenance environments and low noise.

Operates on the Peltier effect for cooling or heating

## INDUSTRY STANDARDS

UR, cUR Recognized; Type 12, 3R, 4, 4X; File No. SA6453

CE

IP 65

## FEATURES

Operates on the Peltier effect for cooling or heating

Contains no refrigerant, making it earth friendly

Filterless design reduces maintenance requirements

Compressor-free air conditioning for demanding indoor and outdoor applications

Prewired with simple terminal block for easy wiring connections

Shrouded and unshrouded models included in standard packages

Operating temperature range -40 C (-40 F) to 55 C (131 F)

Partial recess mount

DC Powered operation for 24V and 48V applications

Low profile design allows for mounting vertically and horizontally on any enclosure to avoid interference with internal components

## SPECIFICATIONS

Table 1/3

| Catalog Number | Article Number | Height | Width | Depth | Nominal Voltage | Nominal Capacity Btu/h |
|----------------|----------------|--------|-------|-------|-----------------|------------------------|
| TE090624010    | 21074          | 236mm  | 128mm | 176mm | 24V             | 178Btu/h               |
| TE090624011    | 21076          | 236mm  | 128mm | 176mm | 24V             | 178Btu/h               |

| CatalogNumber | Article Number | Height | Width | Depth | Nominal Voltage | Nominal Capacity Btu/h |
|---------------|----------------|--------|-------|-------|-----------------|------------------------|
| TE090624020   | 21065          | 230mm  | 123mm | 176mm | 24V             | 178Btu/h               |
| TE121024010   | 21075          | 305mm  | 157mm | 189mm | 24V             | 321Btu/h               |
| TE121024011   | 21072          | 305mm  | 157mm | 189mm | 24V             | 321Btu/h               |
| TE121024020   | 21066          | 300mm  | 153mm | 188mm | 24V             | 321Btu/h               |
| TE121048010   | 21071          | 305mm  | 157mm | 189mm | 48V             | 321Btu/h               |
| TE121048020   | 20812          | 300mm  | 153mm | 188mm | 48V             | 321Btu/h               |
| TE162024010   | 21077          | 405mm  | 187mm | 185mm | 24V             | 567Btu/h               |
| TE162024011   | 21067          | 405mm  | 187mm | 185mm | 24V             | 567Btu/h               |
| TE162024020   | 21068          | 400mm  | 180mm | 184mm | 24V             | 567Btu/h               |
| TE162048010   | 21073          | 405mm  | 187mm | 185mm | 48V             | 567Btu/h               |
| TE162048020   | 21064          | 400mm  | 180mm | 184mm | 48V             | 567Btu/h               |

| Table 2/3      |                |                        |            |             |                       |                     |
|----------------|----------------|------------------------|------------|-------------|-----------------------|---------------------|
| Catalog Number | Article Number | Nominal Capacity Watts | Voltage DC | Max Current | Operating Temperature | Material            |
| TE090624010    | 21074          | 52W                    | 18V        | 4.4A        | -40 to 55°C           | Mild Steel          |
| TE090624011    | 21076          | 52W                    | 18V        | 4.4A        | -40 to 55°C           | Stainless Steel 304 |
| TE090624020    | 21065          | 52W                    | 18V        | 4.4A        | -40 to 55°C           | Aluminum            |
| TE121024010    | 21075          | 94W                    | 18V        | 8.5A        | -40 to 55°C           | Mild Steel          |
| TE121024011    | 21072          | 94W                    | 18V        | 8.5A        | -40 to 55°C           | Stainless Steel 304 |

| CatalogNumber | Article Number | Nominal Capacity Watts | Voltage DC | Max Current | Operating Temperature | Material            |
|---------------|----------------|------------------------|------------|-------------|-----------------------|---------------------|
| TE121024020   | 21066          | 94W                    | 18V        | 8.5A        | -40 to 55°C           | Aluminum            |
| TE121048010   | 21071          | 94W                    | 40V        | 4.4A        | -40 to 55°C           | Mild Steel          |
| TE121048020   | 20812          | 94W                    | 40V        | 4.4A        | -40 to 55°C           | Aluminum            |
| TE162024010   | 21077          | 166W                   | 18V        | 14.7A       | -40 to 55°C           | Mild Steel          |
| TE162024011   | 21067          | 166W                   | 18V        | 14.7A       | -40 to 55°C           | Stainless Steel 304 |
| TE162024020   | 21068          | 166W                   | 18V        | 14.7A       | -40 to 55°C           | Aluminum            |
| TE162048010   | 21073          | 166W                   | 40V        | 7.6A        | -40 to 55°C           | Mild Steel          |
| TE162048020   | 21064          | 166W                   | 40V        | 7.6A        | -40 to 55°C           | Aluminum            |

Table 3/3

| Catalog Number | Article Number | Finish        | Color      | Color Code | Thickness | Quick Ship |
|----------------|----------------|---------------|------------|------------|-----------|------------|
| TE090624010    | 21074          | Powder Coated | Light Gray | RAL 7035   | 1.52mm    | No         |
| TE090624011    | 21076          | Brushed #4    |            |            | 1.52mm    | No         |
| TE090624020    | 21065          | Anodized      |            |            | 1.52mm    | No         |
| TE121024010    | 21075          | Powder Coated | Light Gray | RAL 7035   | 1.52mm    | Yes        |
| TE121024011    | 21072          | Brushed #4    |            |            | 1.52mm    | No         |
| TE121024020    | 21066          | Anodized      |            |            | 1.52mm    | No         |
| TE121048010    | 21071          | Powder Coated | Light Gray | RAL 7035   | 1.52mm    | No         |
| TE121048020    | 20812          | Anodized      |            |            | 1.52mm    | No         |

| CatalogNumber | Article Number | Finish        | Color      | Color Code | Thickness | Quick Ship |
|---------------|----------------|---------------|------------|------------|-----------|------------|
| TE162024010   | 21077          | Powder Coated | Light Gray | RAL 7035   | 1.52mm    | No         |
| TE162024011   | 21067          | Brushed #4    |            |            | 1.52mm    | No         |
| TE162024020   | 21068          | Anodized      |            |            | 1.52mm    | No         |
| TE162048010   | 21073          | Powder Coated | Light Gray | RAL 7035   | 1.52mm    | No         |
| TE162048020   | 21064          | Anodized      |            |            | 1.52mm    | No         |

## WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at [www.nvent.com](http://www.nvent.com) and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.

### North America

All locations  
+1.763.422.2661  
Chat with us:  
[nvent.com/schroff](http://nvent.com/schroff)

### Europe

Straubenhardt, Germany  
+49.7082.794.0  
Betschdorf, France  
+33.3.88.90.64.90  
Warsaw, Poland  
+48.22.209.98.35  
Assago, Italy  
+39.02.932.7141  
Chat with us:  
[nvent.com/schroff](http://nvent.com/schroff)

### Asia

Shanghai, China  
+86.21.2412.6943  
Qingdao, China  
+86.532.8771.6101  
Singapore  
+65.6768.5800  
Shin-Yokohama, Japan  
+81.45.476.0271  
Chat with us:  
[nvent.com/schroff](http://nvent.com/schroff)

### Middle East & India

Dubai, United Arab Emirates  
+971.4.378.1700  
Bangalore, India  
+91.80.6715.2001  
Istanbul, Turkey  
+90.216.250.7374  
Chat with us:  
[nvent.com/schroff](http://nvent.com/schroff)



Our powerful portfolio of brands:

**CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE**