

# XTVR Self-Regulating Heating Cable



nVent RAYCHEM XTVR self-regulating trace heating cables are mainly used for freeze protection of pipes and vessels that require steam cleaning and process temperature maintenance, up to 302 °F/150 °C. They withstand intermittent exposure to 482 °F/250 °C. The fluoropolymer outer jacket (-CT) provides high chemical resistance against aggressive organics and corrosives.

## FEATURES

High power retention (HPR) heating core

Power retention: At least 95% after 10 years

Design life: 30 years or more depending on application

Simplified design in hazardous area: T3 Unconditional or T6-T4 System classification

Longer circuit lengths due to larger cross section conductors

Fast installation: cut-to-length, multiple overlaps allowed, meter markings, user-friendly connections kits

Safe and efficient in operation: no overheating, uniform pipe temperatures, energy saving technology

Reliable during long life: 10 year product warranty available, maintenance free

## SPECIFICATIONS

<b>Max Maintain or Continuous Exposure Temperature, Power On:</b>	150 °C
<b>Supply Voltage:</b>	200 – 277 V
<b>Max Intermittent Exposure Temperature, Power On/Off:</b>	250 °C
<b>Max Cumulative Hours for Intermittent Exposure:</b>	2000 h
<b>Ground Path Type:</b>	Braid
<b>Area Classification:</b>	Non-Hazardous; Hazardous
<b>Outer Jacket Material:</b>	High Temperature Fluoropolymer

Table 1/4

Catalog Number	Item Name	Nominal Power Output @ 10°C, 230V	Color	Conductor Material	Conductor Quantity	Hazardous Area
----------------	-----------	-----------------------------------	-------	--------------------	--------------------	----------------

2000003070	3XTVR2-CT	9 W/m	Red	Tin-Plated Copper	2	Yes
2000003072	5XTVR2-CT	16 W/m	Red	Tin-Plated Copper	2	Yes
2000003073	8XTVR2-CT	25 W/m	Red	Tin-Plated Copper	2	Yes
2000003075	10XTVR2-CT	32 W/m	Red	Tin-Plated Copper	2	Yes
2000003076	12XTVR2-CT	38 W/m	Red	Tin-Plated Copper	2	Yes
2000003078	15XTVR2-CT	48 W/m	Red	Tin-Plated Copper	2	Yes
2000003080	20XTVR2-CT	64 W/m	Red	Tin-Plated Copper	2	Yes

Table 2/4

Catalog Number	Item Name	Max Circuit Length	Max Exposure Temperature	Min Bending Radius @ -60°C	Min Bending Radius @ 20°C	Min Installation Temperature
2000003070	3XTVR2-CT	245 m	250 °C	51 mm	13 mm	-60 °C
2000003072	5XTVR2-CT	233 m	250 °C	51 mm	13 mm	-60 °C
2000003073	8XTVR2-CT	175 m	250 °C	51 mm	13 mm	-60 °C
2000003075	10XTVR2-CT	164 m	250 °C	51 mm	13 mm	-60 °C
2000003076	12XTVR2-CT	140 m	250 °C	51 mm	13 mm	-60 °C
2000003078	15XTVR2-CT	135 m	250 °C	51 mm	13 mm	-60 °C
2000003080	20XTVR2-CT	110 m	250 °C	51 mm	13 mm	-60 °C

Table 3/4

Catalog Number	Item Name	Nominal Cable Weight	Nominal Height	Nominal Power Output @ 10°C, 240V	Nominal Thickness	Nominal Voltage
2000003070	3XTVR2-CT	170 g/m	7.6 mm	9 W/m	7.2 mm	208 V, 220 V, 230 V, 240 V, 277 V

CatalogNumber	Item Name	Nominal Cable Weight	Nominal Height	Nominal Power Output @ 10°C, 240V	Nominal Thickness	Nominal Voltage
2000003072	5XTVR2-CT	170 g/m	7.6 mm	16 W/m	7.2 mm	208 V, 220 V, 230 V, 240 V, 277 V
2000003073	8XTVR2-CT	170 g/m	7.6 mm	26 W/m	7.2 mm	208 V, 220 V, 230 V, 240 V, 277 V
2000003075	10XTVR2-CT	170 g/m	7.6 mm	32 W/m	7.2 mm	208 V, 220 V, 230 V, 240 V, 277 V
2000003076	12XTVR2-CT	170 g/m	7.6 mm	39 W/m	7.2 mm	208 V, 220 V, 230 V, 240 V, 277 V
2000003078	15XTVR2-CT	170 g/m	7.6 mm	49 W/m	7.2 mm	208 V, 220 V, 230 V, 240 V, 277 V
2000003080	20XTVR2-CT	170 g/m	7.6 mm	65 W/m	7.2 mm	208 V, 220 V, 230 V, 240 V, 277 V

Table 4/4

Catalog Number	Item Name	Nominal Width
2000003070	3XTVR2-CT	10.8 mm
2000003072	5XTVR2-CT	10.8 mm
2000003073	8XTVR2-CT	10.8 mm
2000003075	10XTVR2-CT	10.8 mm
2000003076	12XTVR2-CT	10.8 mm
2000003078	15XTVR2-CT	10.8 mm
2000003080	20XTVR2-CT	10.8 mm

## WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at [www.nvent.com](http://www.nvent.com) and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause

product malfunction, property damage, serious bodily injury and death and/or void your warranty.

**North America**

Tel +1.800.545.6258

Fax +1.800.527.5703

[thermal.info@nvent.com](mailto:thermal.info@nvent.com)

**Europe, Middle East,**

**Africa**

Tel +32.16.213.511

Fax +32.16.213.604

[thermal.info@nvent.com](mailto:thermal.info@nvent.com)

**Asia Pacific**

Tel +86.21.2412.1688

Fax +86.21.5426.3167

[cn.thermal.info@nvent.com](mailto:cn.thermal.info@nvent.com)

**Latin America**

Tel +1.713.868.4800

Fax +1.713.868.2333

[thermal.info@nvent.com](mailto:thermal.info@nvent.com)

Our powerful portfolio of brands:

**RAYCHEM PYROTENAX TRACER NUHEAT**