


# Telephone Line Protector



## CERTIFICATIONS



## FEATURES

RJ11 sockets provide simple plug-in connection for 4 or 6 position RJ plugs

Includes patch cord and adhesive mounting strips

Provides both L-L and L-PE protection modes for comprehensive protection


Automatic over-current protection

## SPECIFICATIONS

Catalog Number	SLP1RJ11	SLP1RJ11A
Max Continuous Operating Voltage (Uc)	280 V	280 V
Max Discharge Current (Imax), Per Mode	500kA 8/20 $\mu$ s	20kA 8/20 $\mu$ s
Voltage Protection Level (Up), T-R	110V	110V
Voltage Protection Level (Up), T/R-G	500 V @ 125 A	500 V @ 125 A
Rated Load Current (IL)	160mA	120mA
Connection Type	RJ11	RJ11
Ground Lead Length	150mm	150mm

Catalog Number	SLP1RJ11	SLP1RJ11A
Lead Size	4 mm	4 mm
Temperature	-40 to 65 °C	-40 to 65 °C
Depth (D)	28mm	28mm
Height (H)	38 mm	38 mm
Width (W)	78 mm	78 mm
Unit Weight	0.05 kg	0.05 kg
Certification Details	UL® 497A	
Certifications	UL	

DIAGRAMS



WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at [www.nvent.com](http://www.nvent.com) and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.

North America

+1.800.753.9221  
Option 1 – Customer Care  
Option 2 – Technical  
Support

Europe

Netherlands:  
+31 800-0200135  
France:  
+33 800 901 793

Europe

Germany:  
800 1890272  
Other Countries:  
+31 13 5835404

APAC

Shanghai:  
+ 86 21 2412 1618/19  
Sydney:  
+61 2 9751 8500



Our powerful portfolio of brands:

CADDY   ERICO   HOFFMAN   ILSCO   SCHROFF   TRACHTE