

# Bar Joist Attachment



## CERTIFICATIONS



## FEATURES

Can be installed on bar joists or I-beams

Thumb spring retainer allows for ease of positioning

Snap-off bolt head helps enable easy installation and inspection of seismic sway braces

No assembly required

No loose parts

Meets NFPA®-13 requirements for seismic sway bracing

Meets CEN/TS 17551:2021 requirements for Seismic Sway Bracing

## SPECIFICATIONS

Table 1/2

| Catalog Number | Article Number | Material  | Finish            | Flange Thickness (FT) | Screw Diameter (Sc) | A       |
|----------------|----------------|-----------|-------------------|-----------------------|---------------------|---------|
| CSBBARJEG      | 404354         | Cast Iron | Electrogalvanized | 6.4 - 12.7 mm         | 0.5                 | 50.8 mm |

Table 2/2

| Catalog Number | Article Number | B | C |
|----------------|----------------|---|---|
|----------------|----------------|---|---|

|           |        |         |         |
|-----------|--------|---------|---------|
| CSBBARJEG | 404354 | 76.2 mm | 63.5 mm |
|-----------|--------|---------|---------|


### ADDITIONAL PRODUCT DETAILS

Structure Attachment and Brace Member are not included.

| UL Loads    |                              |                  |                         |             |
|-------------|------------------------------|------------------|-------------------------|-------------|
| Part Number | Structure Attachment Fitting | Flange Thickness | Brace Member            | Load Rating |
| CSBBARJ     | CSBUNIV050                   | 6 - 13 mm        | DN25 - DN50 Sch. 40 NPS | 4004 N      |
|             | CSBURC12                     | 6 - 13 mm        | CSB12CBL                | 1859 N      |
|             |                              |                  | CSB18CBL                | 3434 N      |
|             |                              |                  | CSB36CBL                | 4893 N      |

| FM Loads        |                   |                                                         |          |          |          |
|-----------------|-------------------|---------------------------------------------------------|----------|----------|----------|
| Brace Direction | Service Pipe Size | Horizontal Capacity per Intallation Angle from Vertical |          |          |          |
|                 |                   | 30°- 44°                                                | 45°- 59° | 60°- 74° | 75°- 90° |
| Parallel        | N/A               | 6270 N                                                  | 9385 N   | 11300 N  | 12590 N  |
| Perpendicular   | N/A               | 7740 N                                                  | 7605 N   | 9165 N   | 10230 N  |

### DIAGRAMS



### WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at [www.nvent.com](http://www.nvent.com) and from your nVent customer service representative. Improper

installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.

**North America**

+1.800.753.9221  
Option 1 – Customer Care  
Option 2 – Technical  
Support

**Europe**

Netherlands:  
+31 800-0200135  
France:  
+33 800 901 793

**Europe**

Germany:  
800 1890272  
Other Countries:  
+31 13 5835404

**APAC**

Shanghai:  
+ 86 21 2412 1618/19  
Sydney:  
+61 2 9751 8500



Our powerful portfolio of brands:

CADDY   ERICO   HOFFMAN   ILSCO   SCHROFF   TRACHTE

