We connect and protect

Frame Type Plug-In Unit PCB Mounting Support for Slot 1, 50 Pairs

CATALOG NUMBER

24812-202











PCB is inserted into the guide groove of the left side Panel or that of the rear angle side Panel.

CERTIFICATIONS

RoHS COMPLIANT

FEATURES

- PCB is inserted into the guide groove of the left side Panel or that of the side Panel rear angle
- Fixing occurs when the rear Panel is fitted
- Suitable for frame type plug-in units with guide rails

PRODUCT ATTRIBUTES

- Package Quantity: 100
- Finish: Zinc Plated
- Material: Zinc Alloy
- Product Type: Hardware Kit
- Type: Board Fixing, Slot 1
- Works With: Cassettes
- Net Weight: 0.15kg

ADDITIONAL PRODUCT DETAILS

Torx panhead screw (24560-178) is required to fix PCB without connector. Torx panhead screw (24812-600) is required to fix connector to PCB, in 6 U frame type plug-in units (center).

DIAGRAMS









WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.

North America
All locations
+1.763.422.2661
Chat with us:
nvent.com/schroff

Europe
Straubenhardt, Germany
+49.7082.794.0
Betschdorf, France
+33.3.88.90.64.90
Warsaw, Poland
+48.22.209.98.35
Assago, Italy
+39.02.932.7141
Chat with us:
nvent.com/schroff

Asia
Shanghai, China
+86.21.2412.6943
Qingdao, China
+86.532.8771.6101
Singapore
+65.6768.5800
Shin-Yokohama, Japan
+81.45.476.0271
Chat with us:
nvent.com/schroff

Middle East & India
Dubai, United Arab Emirates
+971.4.378.1700
Bangalore, India
+91.80.6715.2001
Istanbul, Turkey
+90.216.250.7374
Chat with us:
nvent.com/schroff

Our powerful portfolio of brands:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE

©2025 nVent. All nVent marks and logos are owned or licensed by nVent Services GmbH or its affiliates. All other trademarks are the property of their respective owners. nVent reserves the right to change specifications without notice.

This document is system-generated.