

nVent CADDY Cat HP J-Hook with Pin Driven Angle Bracket, 100 mm dia, 9 mm Hole

Data Solutions

CATALOG NUMBER

CAT64HPAFAB6



CERTIFICATIONS



FEATURES

Longer leg angle bracket for tool clearance

Designed to fit a variety of pin drivers

Provides optimal support for high-performance data cable, up to and including Cat 5e, Cat 6, Cat 6A, Cat 7 and fibre optic

Provides superior fill capacity and load rating over most other non-continuous cable support alternatives

Rounded edges on J-Hooks provide proper bend radius support for high performance data cables

Cost effective alternative to expensive cable tray

Complies with EN 50174-2

Meets ISO®/IEC 14763-2, ANSI®/TIA 568 and ANSI®/TIA 569

PRODUCT ATTRIBUTES


Article Number: 181225
Material: Steel
Finish: Pregalvanized
Diameter (Ø): 100mm
Area: 9987mm²
Cable Capacity, Cat 5e: 330
Cable Capacity, Cat 6: 220
Cable Capacity, Cat 6A: 140
Hole Size (HS): 9mm
Static Load: 270N

ADDITIONAL PRODUCT DETAILS

Non-continuous supports may not exceed spacing of 5' (1.5 m) per TIA 569-C.9.7 and EN 50174-2.

Cable capacity is calculated based on a 70% fill rate.

DIAGRAMS



WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.



Our powerful portfolio of brands:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE