

# nVent ERIFLEX FleXbus Splicing Blocks



The nVent ERIFLEX Splicing Blocks are designed for extending FleXbus conductors with a strong, compact design that ensures high short-circuit resistance and easy installation in various positions. They support extensions above 25 meters for 220-960mm² conductors and above 15 meters for 1280-1810mm² conductors. The blocks feature a powder-painted aluminum connector to prevent galvanic corrosion and nonmagnetic stainless steel screws.

The flexible insulated cover provides Class II insulation, resists high temperatures up to 115°C, has an IP55 rating for water and dust protection, and is treated to resist rodent and termite attacks. The blocks comply with IEC 61 439-1 and IEC 60 364 standards and carry CE and UKCA certifications.

#### **CERTIFICATIONS**



# **FEATURES**

Strong and compact design for high short-circuit resistance

High-temperature resistant cover treated against rodent and termite attacks

Compliance with IEC standards and CE/UKCA certifications

Multiple connection options: vertical, horizontal, flat position, or on edge

Durable and reliable performance in various applications

IP55 water and dust resistance

UV-resistant material

Flame-retardant, Low smoke, Halogen-free

# **SPECIFICATIONS**

Insulation Thickness: 3 mm

Temperature:

**Dielectric Strength:** 20kV/mm

Material: Thermoplastic Elastomer; Ethylene Propylene Rubber

IEC® 60695-2-11 (Glow Wire Test 960 °C);IEC® 61439.1;IEC® 61439.1 Class II;IEC® **Complies With:** 

UL® 2885;IEC® 60754-1;IEC® 62821-2 **Halogen Free Rating:** UL® 2885;IEC® 61034-2;ISO 5659-2 Low Smoke Rating:

IP Rating: IP55


**Rodent & Termite Proof:** Tested as per GB/T 34016-2017 & DIN EN 117

**UV Resistance Rating:** UL® 2556;UL® 854

Flammability Rating: UL® 94V-0 **Working Temperature:** -50 to 115 °C 500 % Max **Insulation Elongation:** 

| Table 1/1         |                |                   |        |        |        |             |
|-------------------|----------------|-------------------|--------|--------|--------|-------------|
| Catalog<br>Number | Article Number | Cross Section     | A      | В      | С      | Unit Weight |
| FLEXSB1280        | 508166         | 1280mm²           | 322 mm | 169 mm | 150 mm | 5.9 kg      |
| FLEXSB1810        | 508167         | 1810mm²           | 322 mm | 169 mm | 150 mm | 6.2 kg      |
| FLEXSB220-360     | 508163         | 220mm²,<br>360mm² | 264 mm | 111 mm | 120 mm | 2.1 kg      |
| FLEXSB545-640     | 508164         | 545mm²,<br>640mm² | 228 mm | 111 mm | 133 mm | 2.3 kg      |
| FLEXSB800-960     | 508165         | 800mm²,<br>960mm² | 322 mm | 169 mm | 150 mm | 5.7 kg      |

## **DIAGRAMS**



#### **WARNING**

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.

#### **North America**

+1.800.753.9221 Option 1 – Customer Care Option 2 – Technical Support

# Europe

Netherlands: +31 800-0200135 France: +33 800 901 793

# **Europe**

Germany: 800 1890272 Other Countries: +31 13 5835404

## **APAC**

Shanghai: + 86 21 2412 1618/19 Sydney: +61 2 9751 8500



Our powerful portfolio of brands:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE