

nVent ERICO Ericore Terminated Conductor



FEATURES

Low-inductance, low-impedance cable designed to minimize voltage build-up due to lightning impulses

Multiple insulated layers of conductor reduce the potential of side flashing

Upper termination provides an insulated connection from terminal to nVent ERICO Ericore to properly transition the lightning strike

Requires lower termination kit

SPECIFICATIONS

Table 1/2

Catalog Number	Length (L)	Capacitance	Cross Section	Diameter (Ø)
ERICORE054T	54m	0.75 nF		36 mm
ERICORE049T	49m	0.75 nF		36 mm
ERICORE097T	97m	0.75 nF		36 mm
ERICORE050T	50m	0.75 nF		36 mm
ERICORE010T	10m	0.75 nF		36 mm
ERICORE107T	107m	0.75 nF		36 mm

Catalog Number	Length (L)	Capacitance	Cross Section	Diameter (Ø)
ERICORE033T	33m	0.75 nF		36 mm
ERICORE051T	51m	0.75 nF		36 mm
ERICORE095T	95m	0.75 nF		36 mm
ERICORE052T	52m	0.75 nF		36 mm
ERICORE032T	32m	0.75 nF		36 mm
ERICORE155T	155m	0.75 nF		36 mm
ERICORE053T	53m	0.75 nF		36 mm
ERICORE009T	9m	0.75 nF		36 mm
ERICORE092T	92m	0.75 nF		36 mm
ERICORE034T	34m	0.75 nF		36 mm
ERICORE016T	16m	0.75 nF		36 mm
ERICORE110T	110m	0.75 nF		36 mm
ERICORE031T	31m	0.75 nF		36 mm
ERICORE055T	55m	0.75 nF		36 mm
ERICORE091T	91m	0.75 nF		36 mm
ERICORE030T	30m	0.75 nF		36 mm
ERICORE008T	8m	0.75 nF		36 mm
ERICORE056T	56m	0.75 nF		36 mm

Catalog Number	Length (L)	Capacitance	Cross Section	Diameter (Ø)
ERICORE090T	90m	0.75 nF		36 mm
ERICORE112T	112m	0.75 nF		36 mm
ERICORE057T	57m	0.75 nF		36 mm
ERICORE029T	29m	0.75 nF		36 mm
ERICORE058T	58m	0.75 nF		36 mm
ERICORE088T	88m	0.75 nF		36 mm
ERICORE012T	12m	0.75 nF		36 mm
ERICORE039T	39m	0.75 nF		36 mm
ERICORE104T	104m	0.75 nF		36 mm
ERICORE040T	40m	0.75 nF		36 mm
ERICORE038T	38m	0.75 nF		36 mm
ERICORE013T	13m	0.75 nF		36 mm
ERICORE041T	41m	0.75 nF		36 mm
ERICORE102T	102m	0.75 nF		36 mm
ERICORE014T	14m	0.75 nF		36 mm
ERICORE042T	42m	0.75 nF		36 mm
ERICORE105T	105m	0.75 nF		36 mm
ERICORE037T	37m	0.75 nF		36 mm

Catalog Number	Length (L)	Capacitance	Cross Section	Diameter (Ø)
ERICORE043T	43m	0.75 nF		36 mm
ERICORE101T	101m	0.75 nF		36 mm
ERICORE150T	150m	0.75 nF		36 mm
ERICORE020T	20m	0.75 nF		36 mm
ERICORE044T	44m	0.75 nF		36 mm
ERICORE036T	36m	0.75 nF		36 mm
ERICORE045T	45m	0.75 nF		36 mm
ERICORE100T	100m	0.75 nF		36 mm
ERICORE046T	46m	0.75 nF		36 mm
ERICORE106T	106m	0.75 nF		36 mm
ERICORE035T	35m	0.75 nF		36 mm
ERICORE011T	11m	0.75 nF		36 mm
ERICORE047T	47m	0.75 nF		36 mm
ERICORE098T	98m	0.75 nF		36 mm
ERICORE015T	15m	0.75 nF		36 mm
ERICORE048T	48m	0.75 nF		36 mm
ERICORE136T	136m	0.75 nF		36 mm
ERICORE003T	3m	0.75 nF		36 mm

Catalog Number	Length (L)	Capacitance	Cross Section	Diameter (Ø)
ERICORE025T	25m	0.75 nF		36 mm
ERICORE083T	83m	0.75 nF		36 mm
ERICORE067T	67m	0.75 nF		36 mm
ERICORE120T	120m	0.75 nF		36 mm
ERICORE018T	18m	0.75 nF		36 mm
ERICORE005T	5m	0.75 nF		36 mm
ERICORE082T	82m	0.75 nF		36 mm
ERICORE024T	24m	0.75 nF		36 mm
ERICORE068T	68m	0.75 nF		36 mm
ERICORE125T	125m	0.75 nF		36 mm
ERICORE081T	81m	0.75 nF		36 mm
ERICORE069T	69m	0.75 nF		36 mm
ERICORE023T	23m	0.75 nF		36 mm
ERICORE080T	80m	0.75 nF		36 mm
ERICORE007T	7m	0.75 nF	50mm ²	36 mm
ERICORE070T	70m	0.75 nF		36 mm
ERICORE078T	78m	0.75 nF		36 mm
ERICORE022T	22m	0.75 nF		36 mm

Catalog Number	Length (L)	Capacitance	Cross Section	Diameter (Ø)
ERICORE071T	71m	0.75 nF		36 mm
ERICORE122T	122m	0.75 nF		36 mm
ERICORE077T	77m	0.75 nF		36 mm
ERICORE021T	21m	0.75 nF		36 mm
ERICORE200T	200m	0.75 nF		36 mm
ERICORE072T	72m	0.75 nF		36 mm
ERICORE001T	1m	0.75 nF		36 mm
ERICORE019T	19m	0.75 nF		36 mm
ERICORE076T	76m	0.75 nF		36 mm
ERICORE075T	75m	0.75 nF		36 mm
ERICORE006T	6m	0.75 nF		36 mm
ERICORE086T	86m	0.75 nF		36 mm
ERICORE028T	28m	0.75 nF		36 mm
ERICORE026T	26m	0.75 nF		36 mm
ERICORE087T	87m	0.75 nF		36 mm
ERICORE168T	168m	0.75 nF		36 mm
ERICORE017T	17m	0.75 nF		36 mm
ERICORE065T	65m	0.75 nF		36 mm

Catalog Number	Length (L)	Capacitance	Cross Section	Diameter (Ø)
ERICORE060T	60m	0.75 nF		36 mm
ERICORE085T	85m	0.75 nF		36 mm
ERICORE064T	64m	0.75 nF		36 mm
ERICORE061T	61m	0.75 nF		36 mm
ERICORE066T	66m	0.75 nF		36 mm
ERICORE115T	115m	0.75 nF		36 mm

Table 2/2

Catalog Number	Impedance	Inductance	Resistance (Rdc)	Resistance (Rimp)	Upper Termination Voltage Withstand	Unit Weight
ERICORE054T	12 Ω Max	37nH	0.5mΩ·m	6mΩ·m	250kV	65.46 kg
ERICORE049T	12 Ω Max	37nH	0.5mΩ·m	6mΩ·m	250kV	59.56 kg
ERICORE097T	12 Ω Max	37nH	0.5mΩ·m	6mΩ·m	250kV	116.2 kg
ERICORE050T	12 Ω Max	37nH	0.5mΩ·m	6mΩ·m	250kV	60.74 kg
ERICORE010T	12 Ω Max	37nH	0.5mΩ·m	6mΩ·m	250kV	13.54 kg
ERICORE107T	12 Ω Max	37nH	0.5mΩ·m	6mΩ·m	250kV	128 kg
ERICORE033T	12 Ω Max	37nH	0.5mΩ·m	6mΩ·m	250kV	40.68 kg
ERICORE051T	12 Ω Max	37nH	0.5mΩ·m	6mΩ·m	250kV	61.92 kg
ERICORE095T	12 Ω Max	37nH	0.5mΩ·m	6mΩ·m	250kV	113.84 kg
ERICORE052T	12 Ω Max	37nH	0.5mΩ·m	6mΩ·m	250kV	63.1 kg

CatalogNumber	Impedance	Inductance	Resistance (Rdc)	Resistance (Rimp)	Upper Termination Voltage Withstand	Unit Weight
ERICORE032T	12 Ω Max	37nH	0.5mΩ·m	6mΩ·m	250kV	39.5 kg
ERICORE155T	12 Ω Max	37nH	0.5mΩ·m	6mΩ·m	250kV	184.64 kg
ERICORE053T	12 Ω Max	37nH	0.5mΩ·m	6mΩ·m	250kV	64.28 kg
ERICORE009T	12 Ω Max	37nH	0.5mΩ·m	6mΩ·m	250kV	12.36 kg
ERICORE092T	12 Ω Max	37nH	0.5mΩ·m	6mΩ·m	250kV	110.3 kg
ERICORE034T	12 Ω Max	37nH	0.5mΩ·m	6mΩ·m	250kV	41.86 kg
ERICORE016T	12 Ω Max	37nH	0.5mΩ·m	6mΩ·m	250kV	20.62 kg
ERICORE110T	12 Ω Max	37nH	0.5mΩ·m	6mΩ·m	250kV	131.54 kg
ERICORE031T	12 Ω Max	37nH	0.5mΩ·m	6mΩ·m	250kV	38.32 kg
ERICORE055T	12 Ω Max	37nH	0.5mΩ·m	6mΩ·m	250kV	66.64 kg
ERICORE091T	12 Ω Max	37nH	0.5mΩ·m	6mΩ·m	250kV	109.12 kg
ERICORE030T	12 Ω Max	37nH	0.5mΩ·m	6mΩ·m	250kV	37.14 kg
ERICORE008T	12 Ω Max	37nH	0.5mΩ·m	6mΩ·m	250kV	11.18 kg
ERICORE056T	12 Ω Max	37nH	0.5mΩ·m	6mΩ·m	250kV	67.82 kg
ERICORE090T	12 Ω Max	37nH	0.5mΩ·m	6mΩ·m	250kV	107.94 kg
ERICORE112T	12 Ω Max	37nH	0.5mΩ·m	6mΩ·m	250kV	133.9 kg
ERICORE057T	12 Ω Max	37nH	0.5mΩ·m	6mΩ·m	250kV	69 kg

CatalogNumber	Impedance	Inductance	Resistance (Rdc)	Resistance (Rimp)	Upper Termination Voltage Withstand	Unit Weight
ERICORE029T	12 Ω Max	37nH	0.5mΩ·m	6mΩ·m	250kV	35.96 kg
ERICORE058T	12 Ω Max	37nH	0.5mΩ·m	6mΩ·m	250kV	70.18 kg
ERICORE088T	12 Ω Max	37nH	0.5mΩ·m	6mΩ·m	250kV	105.58 kg
ERICORE012T	12 Ω Max	37nH	0.5mΩ·m	6mΩ·m	250kV	15.9 kg
ERICORE039T	12 Ω Max	37nH	0.5mΩ·m	6mΩ·m	250kV	47.76 kg
ERICORE104T	12 Ω Max	37nH	0.5mΩ·m	6mΩ·m	250kV	124.46 kg
ERICORE040T	12 Ω Max	37nH	0.5mΩ·m	6mΩ·m	250kV	48.94 kg
ERICORE038T	12 Ω Max	37nH	0.5mΩ·m	6mΩ·m	250kV	46.58 kg
ERICORE013T	12 Ω Max	37nH	0.5mΩ·m	6mΩ·m	250kV	17.08 kg
ERICORE041T	12 Ω Max	37nH	0.5mΩ·m	6mΩ·m	250kV	50.12 kg
ERICORE102T	12 Ω Max	37nH	0.5mΩ·m	6mΩ·m	250kV	122.1 kg
ERICORE014T	12 Ω Max	37nH	0.5mΩ·m	6mΩ·m	250kV	18.26 kg
ERICORE042T	12 Ω Max	37nH	0.5mΩ·m	6mΩ·m	250kV	51.3 kg
ERICORE105T	12 Ω Max	37nH	0.5mΩ·m	6mΩ·m	250kV	125.64 kg
ERICORE037T	12 Ω Max	37nH	0.5mΩ·m	6mΩ·m	250kV	45.4 kg
ERICORE043T	12 Ω Max	37nH	0.5mΩ·m	6mΩ·m	250kV	52.48 kg
ERICORE101T	12 Ω Max	37nH	0.5mΩ·m	6mΩ·m	250kV	120.92 kg

CatalogNumber	Impedance	Inductance	Resistance (Rdc)	Resistance (Rimp)	Upper Termination Voltage Withstand	Unit Weight
ERICORE150T	12 Ω Max	37nH	0.5m Ω ·m	6m Ω ·m	250kV	178.74 kg
ERICORE020T	12 Ω Max	37nH	0.5m Ω ·m	6m Ω ·m	250kV	25.34 kg
ERICORE044T	12 Ω Max	37nH	0.5m Ω ·m	6m Ω ·m	250kV	53.66 kg
ERICORE036T	12 Ω Max	37nH	0.5m Ω ·m	6m Ω ·m	250kV	44.22 kg
ERICORE045T	12 Ω Max	37nH	0.5m Ω ·m	6m Ω ·m	250kV	54.84 kg
ERICORE100T	12 Ω Max	37nH	0.5m Ω ·m	6m Ω ·m	250kV	119.74 kg
ERICORE046T	12 Ω Max	37nH	0.5m Ω ·m	6m Ω ·m	250kV	56.02 kg
ERICORE106T	12 Ω Max	37nH	0.5m Ω ·m	6m Ω ·m	250kV	126.82 kg
ERICORE035T	12 Ω Max	37nH	0.5m Ω ·m	6m Ω ·m	250kV	43.04 kg
ERICORE011T	12 Ω Max	37nH	0.5m Ω ·m	6m Ω ·m	250kV	14.72 kg
ERICORE047T	12 Ω Max	37nH	0.5m Ω ·m	6m Ω ·m	250kV	57.2 kg
ERICORE098T	12 Ω Max	37nH	0.5m Ω ·m	6m Ω ·m	250kV	117.38 kg
ERICORE015T	12 Ω Max	37nH	0.5m Ω ·m	6m Ω ·m	250kV	19.44 kg
ERICORE048T	12 Ω Max	37nH	0.5m Ω ·m	6m Ω ·m	250kV	58.38 kg
ERICORE136T	12 Ω Max	37nH	0.5m Ω ·m	6m Ω ·m	250kV	162.22 kg
ERICORE003T	12 Ω Max	37nH	0.5m Ω ·m	6m Ω ·m	250kV	5.28 kg
ERICORE025T	12 Ω Max	37nH	0.5m Ω ·m	6m Ω ·m	250kV	31.24 kg

CatalogNumber	Impedance	Inductance	Resistance (Rdc)	Resistance (Rimp)	Upper Termination Voltage Withstand	Unit Weight
ERICORE083T	12 Ω Max	37nH	0.5m Ω ·m	6m Ω ·m	250kV	99.68 kg
ERICORE067T	12 Ω Max	37nH	0.5m Ω ·m	6m Ω ·m	250kV	80.8 kg
ERICORE120T	12 Ω Max	37nH	0.5m Ω ·m	6m Ω ·m	250kV	143.34 kg
ERICORE018T	12 Ω Max	37nH	0.5m Ω ·m	6m Ω ·m	250kV	22.98 kg
ERICORE005T	12 Ω Max	37nH	0.5m Ω ·m	6m Ω ·m	250kV	7.64 kg
ERICORE082T	12 Ω Max	37nH	0.5m Ω ·m	6m Ω ·m	250kV	98.5 kg
ERICORE024T	12 Ω Max	37nH	0.5m Ω ·m	6m Ω ·m	250kV	30.06 kg
ERICORE068T	12 Ω Max	37nH	0.5m Ω ·m	6m Ω ·m	250kV	81.98 kg
ERICORE125T	12 Ω Max	37nH	0.5m Ω ·m	6m Ω ·m	250kV	149.24 kg
ERICORE081T	12 Ω Max	37nH	0.5m Ω ·m	6m Ω ·m	250kV	97.32 kg
ERICORE069T	12 Ω Max	37nH	0.5m Ω ·m	6m Ω ·m	250kV	83.16 kg
ERICORE023T	12 Ω Max	37nH	0.5m Ω ·m	6m Ω ·m	250kV	28.88 kg
ERICORE080T	12 Ω Max	37nH	0.5m Ω ·m	6m Ω ·m	250kV	96.14 kg
ERICORE007T	12 Ω Max	37nH	0.5m Ω ·m	6m Ω ·m	250kV	10 kg
ERICORE070T	12 Ω Max	37nH	0.5m Ω ·m	6m Ω ·m	250kV	84.34 kg
ERICORE078T	12 Ω Max	37nH	0.5m Ω ·m	6m Ω ·m	250kV	93.78 kg
ERICORE022T	12 Ω Max	37nH	0.5m Ω ·m	6m Ω ·m	250kV	27.7 kg

CatalogNumber	Impedance	Inductance	Resistance (Rdc)	Resistance (Rimp)	Upper Termination Voltage Withstand	Unit Weight
ERICORE071T	12 Ω Max	37nH	0.5mΩ·m	6mΩ·m	250kV	85.52 kg
ERICORE122T	12 Ω Max	37nH	0.5mΩ·m	6mΩ·m	250kV	145.7 kg
ERICORE077T	12 Ω Max	37nH	0.5mΩ·m	6mΩ·m	250kV	92.6 kg
ERICORE021T	12 Ω Max	37nH	0.5mΩ·m	6mΩ·m	250kV	26.52 kg
ERICORE200T	12 Ω Max	37nH	0.5mΩ·m	6mΩ·m	250kV	237.74 kg
ERICORE072T	12 Ω Max	37nH	0.5mΩ·m	6mΩ·m	250kV	86.7 kg
ERICORE001T	12 Ω Max	37nH	0.5mΩ·m	6mΩ·m	250kV	2.92 kg
ERICORE019T	12 Ω Max	37nH	0.5mΩ·m	6mΩ·m	250kV	24.16 kg
ERICORE076T	12 Ω Max	37nH	0.5mΩ·m	6mΩ·m	250kV	91.42 kg
ERICORE075T	12 Ω Max	37nH	0.5mΩ·m	6mΩ·m	250kV	90.24 kg
ERICORE006T	12 Ω Max	37nH	0.5mΩ·m	6mΩ·m	250kV	8.82 kg
ERICORE086T	12 Ω Max	37nH	0.5mΩ·m	6mΩ·m	250kV	103.22 kg
ERICORE028T	12 Ω Max	37nH	0.5mΩ·m	6mΩ·m	250kV	34.78 kg
ERICORE026T	12 Ω Max	37nH	0.5mΩ·m	6mΩ·m	250kV	32.42 kg
ERICORE087T	12 Ω Max	37nH	0.5mΩ·m	6mΩ·m	250kV	104.4 kg
ERICORE168T	12 Ω Max	37nH	0.5mΩ·m	6mΩ·m	250kV	199.98 kg
ERICORE017T	12 Ω Max	37nH	0.5mΩ·m	6mΩ·m	250kV	21.8 kg

CatalogNumber	Impedance	Inductance	Resistance (Rdc)	Resistance (Rimp)	Upper Termination Voltage Withstand	Unit Weight
ERICORE065T	12 Ω Max	37nH	0.5m Ω ·m	6m Ω ·m	250kV	78.44 kg
ERICORE060T	12 Ω Max	37nH	0.5m Ω ·m	6m Ω ·m	250kV	72.54 kg
ERICORE085T	12 Ω Max	37nH	0.5m Ω ·m	6m Ω ·m	250kV	102.04 kg
ERICORE064T	12 Ω Max	37nH	0.5m Ω ·m	6m Ω ·m	250kV	77.26 kg
ERICORE061T	12 Ω Max	37nH	0.5m Ω ·m	6m Ω ·m	250kV	73.72 kg
ERICORE066T	12 Ω Max	37nH	0.5m Ω ·m	6m Ω ·m	250kV	79.62 kg
ERICORE115T	12 Ω Max	37nH	0.5m Ω ·m	6m Ω ·m	250kV	137.44 kg

ADDITIONAL PRODUCT DETAILS

Additional lengths available in 1 m (3.28') increments.

Consult nVent ERICO technical support or the installation manual for guidance on maximum allowable lengths.

Inductance and Capacitance are per meter.

DIAGRAMS



WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.

North America

+1.800.753.9221
Option 1 – Customer Care
Option 2 – Technical
Support

Europe

Netherlands:
+31 800-0200135
France:
+33 800 901 793

Europe

Germany:
800 1890272
Other Countries:
+31 13 5835404

APAC

Shanghai:
+ 86 21 2412 1618/19
Sydney:
+61 2 9751 8500



Our powerful portfolio of brands:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE