

# Neutral Bar for TD Distribution Blocks



## CERTIFICATIONS



## FEATURES

Attaches to four pole distribution blocks for increased wire capacity

Direct electrical connection

Strong mechanical assembly

Transparent protection cover

Halogen free

RoHS compliant


Conforms to EN 45545 obtaining an HL3 classification for chapter R23 and HL2 classification for chapter R22

## SPECIFICATIONS

| Catalog Number                        | NB-125A | NB-160A |
|---------------------------------------|---------|---------|
| Article Number                        | 563841  | 563201  |
| Max Current Rating, IEC               | 125A    | 160A    |
| Short Term Withstand Current (Icw) 1s | 4.5kA   | 6.2kA   |
| Peak Short Circuit Current (Ipk)      | 30kA    | 35kA    |

| Catalog Number                         | NB-125A                                         | NB-160A                               |
|----------------------------------------|-------------------------------------------------|---------------------------------------|
| Line Side Number of Connections        | 3                                               | 4                                     |
| Line Side Compact Stranded Wire Size   | 10 - 25 mm <sup>2</sup>                         | 10 - 35 mm <sup>2</sup>               |
| Line Side Stranded Wire Size - Ferrule | 6 - 16 mm <sup>2</sup>                          | 10 - 25 mm <sup>2</sup>               |
| Load Side Number of Connections        | 9                                               | 10                                    |
| Load Side Compact Stranded Wire Size   | 2,5 - 6 mm <sup>2</sup>                         | 2,5 - 16 mm <sup>2</sup>              |
| Load Side Stranded Wire Size - Ferrule | 1,5 – 6 mm <sup>2</sup>                         | 1,5 – 16 mm <sup>2</sup>              |
| Depth (D)                              | 37.4mm                                          | 41.4mm                                |
| Height (H)                             | 34.3 mm                                         | 34.3 mm                               |
| Width (W)                              | 142 mm                                          | 170 mm                                |
| Unit Weight                            | 0.17 kg                                         | 0.2 kg                                |
| For Use With                           | TD-100-125AL (563830)<br>TD-100-125ALL (563840) | TD-160A (563200)<br>TD-160AL (563990) |
| Flammability Rating                    | UL® 94V-0                                       | UL® 94V-0                             |
| Complies With                          | IEC® 60947-7-1                                  | IEC® 60947-7-1                        |

## DIAGRAMS



## WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at [www.nvent.com](http://www.nvent.com) and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.

#### North America

+1.800.753.9221

Option 1 – Customer Care

Option 2 – Technical

Support

#### Europe

Netherlands:

+31 800-0200135

France:

+33 800 901 793

#### Europe

Germany:

800 1890272

Other Countries:

+31 13 5835404

#### APAC

Shanghai:

+ 86 21 2412 1618/19

Sydney:

+61 2 9751 8500



Our powerful portfolio of brands:

**CADDY**

**ERICO**

**HOFFMAN**

**ILSCO**

**SCHROFF**

**TRACHTE**