



# 1-Phase 110V 30A basic PDU drawing & specification

## Basic Strip



Circuit A



### Single phase basic PDU

Input Rating : 30A, 110V  
 Outlet : 20A Rated US NEMA 5-20R x 24  
 Inlet : 30A NEMA L5-30P plug  
 Cordset : 3 meter UL 10AWG cordset  
 Protection : NIL  
 Circuit Details : < **Circuit A** > Output 12A max. U.S # 1 - 12  
                   < **Circuit B** > Output 12A max. U.S # 13 - 24

Operating Temperature : -5 to 60 °C  
 Storage Temperature : -25 to 65 °C  
 Operating Altitude : 0 to 2,000 m  
 Storage Altitude : 0 to 15,000 m  
 Humidity : 8 to 95% RH, non-condensing

EMC Compliance : FCC Part 15 Subpart B certified  
 Safety Compliance : cTUVus Mark to UL 60950-1:2007/R:2014-10  
                           CAN/CSA-C22.2 No. 60950-1:2007/A2:2014-10  
                           UL 62368-1:2014  
                           CAN/CSA-C22.2 No. 62368-1:2014  
                           UL 60730-1 Ed.5 (2016)

Environment Compliance : RoHS2 & REACH

Chassis Material : Steel  
 Chassis Color : Black

Product Dimension : 2.1 (W) x 3.1 (D) x 43.3 (H) inch  
 Net Weight : 16.1 lbs

Packing dimension ( for 2 PDUs ) : 4.3 (W) x 10.6 (D) x 54.8 (H) inch  
 PDU gross weight ( for 2 PDUs ) : 39.95 lbs