

# Universal Restraint Clip



## CERTIFICATIONS



## FEATURES

Attaches cable brace to structure

Meets CEN/TS 17551:2021 requirements for Seismic Sway Bracing

## SPECIFICATIONS

Table 1/2

| Catalog Number | Article Number | Material                        | Finish            | Brace Size    | Hole Size (HS) | Thickness (T) |
|----------------|----------------|---------------------------------|-------------------|---------------|----------------|---------------|
| CSBURC38SS     | 402522         | Stainless Steel 316 (EN 1.4401) |                   | #12, #18, #36 | 11 mm          | 4.27 mm       |
| CSBURC38       | 402198         | Steel                           | Electrogalvanized | #12, #18, #36 | 11 mm          | 4.27 mm       |
| CSBURC58SS     | 402564         | Stainless Steel 316 (EN 1.4401) |                   | #12, #18, #36 | 17 mm          | 4.27 mm       |
| CSBURC58       | 402200         | Steel                           | Electrogalvanized | #12, #18, #36 | 17 mm          | 4.27 mm       |

| CatalogNumber | Article Number | Material | Finish                | Brace Size    | Hole Size (HS) | Thickness (T) |
|---------------|----------------|----------|-----------------------|---------------|----------------|---------------|
| CSBURC12      | 402199         | Steel    | Electrogalvaniz<br>ed | #12, #18, #36 | 14 mm          | 4.27 mm       |

Table 2/2

| Catalog Number | Article Number | UL Listed Load | Certifications                                               |
|----------------|----------------|----------------|--------------------------------------------------------------|
| CSBURC38SS     | 402522         | 2750N          |                                                              |
| CSBURC38       | 402198         | 3430N          | OSHDPD/HCAI, UL, cUL, ICC-ES (Seismic Cable Bracing), ICC-ES |
| CSBURC58SS     | 402564         | 2750N          |                                                              |
| CSBURC58       | 402200         | 3430N          | ICC-ES (Seismic Cable Bracing), ICC-ES, UL, cUL, OSHDPD/HCAI |
| CSBURC12       | 402199         | 3430N          | ICC-ES (Seismic Cable Bracing), ICC-ES, OSHDPD/HCAI, UL, cUL |


## ADDITIONAL PRODUCT DETAILS

Brace member is not included.

Mount to the structure using the center hole. Loop cable through the holes in the bent tabs and swage in place.

| UL Loads    |              |             |
|-------------|--------------|-------------|
| Part Number | Brace Member | Load Rating |
| CSBURC38    | CSB12CBL     | 1859 N      |
|             | CSB18CBL     | 3434 N      |
|             | CSB36CBL     | 8492 N      |
| CSBURC12    | CSB12CBL     | 1859 N      |
|             | CSB18CBL     | 3434 N      |
|             | CSB36CBL     | 8492 N      |
| CSBURC58    | CSB12CBL     | 1859 N      |
|             | CSB18CBL     | 3434 N      |
|             | CSB36CBL     | 8492 N      |

DIAGRAMS



WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at [www.nvent.com](http://www.nvent.com) and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.

North America

+1.800.753.9221  
Option 1 – Customer Care  
Option 2 – Technical  
Support

Europe

Netherlands:  
+31 800-0200135  
France:  
+33 800 901 793

Europe

Germany:  
800 1890272  
Other Countries:  
+31 13 5835404

APAC

Shanghai:  
+ 86 21 2412 1618/19  
Sydney:  
+61 2 9751 8500



Our powerful portfolio of brands:

CADDY   ERICO   HOFFMAN   ILSCO   SCHROFF   TRACHTE

