

# **nVent CADDY Speed Link Catenary Kit**



#### **FEATURES**

Kit includes precut length of fuse-cut cable to avoid fraying, pre-assembled hook end fitting and tool-free locking device to save installation time

Fastens to the building structure by looping around and hooking to wire rope

Hook end-fitting easily attaches to eye nut

Spring latch helps provide secure connection

#### **SPECIFICATIONS**

Wire Rope Diameter: 6 mm

Finish: Electrogalvanized;Hot-Dip Galvanized

Material: Steel;Zinc Alloy;Polypropylene

Table 1/2						
Catalog Number	Article Number	Wire Rope Length	A	В	С	Height (H)
SLK6L10	196801	10m	75 mm	40 mm	15 mm	108 mm
SLK6L15	196802	15m	75 mm	40 mm	15 mm	108 mm
SLK6L20	196803	20m	75 mm	40 mm	15 mm	108 mm
SLK6L25	196804	25m	75 mm	40 mm	15 mm	108 mm

CatalogNumber	Article Number	Wire Rope Length	A	В	С	Height (H)
SLK6L30	196805	30m	75 mm	40 mm	15 mm	108 mm
SLK6L40	196806	40m	75 mm	40 mm	15 mm	108 mm
SLK6L5	196800	5m	75 mm	40 mm	15 mm	108 mm
SLK6L50	196807	50m	75 mm	40 mm	15 mm	108 mm

Table 2/2					
<b>Catalog Number</b>	Article Number	Width (W)	Thickness (T)	Angle (a)	
SLK6L10	196801	41 mm	30 mm	60 ° Max	
SLK6L15	196802	41 mm	30 mm	60 ° Max	
SLK6L20	196803	41 mm	30 mm	60 ° Max	
SLK6L25	196804	41 mm	30 mm	60 ° Max	
SLK6L30	196805	41 mm	30 mm	60 ° Max	
SLK6L40	196806	41 mm	30 mm	60 ° Max	
SLK6L5	196800	41 mm	30 mm	60 ° Max	
SLK6L50	196807	41 mm	30 mm	60 ° Max	

## ADDITIONAL PRODUCT DETAILS


Wire Rope Length is measured from the end of the wire rope to the hook side of the swage.


Static load 1 represents a point load in the center of the catenary installation. Static load 2 represents a two or three point distributed load on the catenary installation. Static load 3 represents a four or more point distributed load on the catenary installation.


Preload of the wire rope must be applied using Catenary Tensioning Tool.

Horizontal Intallation				
Preload	1000 N	450 N		
Static Load 1 (F1)	490 N	590 N		
Static Load 2 (F2)	880 N	1080 N		
Static Load 3 (F3)	980 N	1180 N		
Vertical Installation				
Static Load 4 (F4)	4440 N			

### **DIAGRAMS**









#### WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.

## North America

+1.800.753.9221 Option 1 – Customer Care Option 2 – Technical Support

# Europe

Netherlands: +31 800-0200135 France: +33 800 901 793

#### **Europe**

Germany: 800 1890272 Other Countries: +31 13 5835404

#### **APAC**

Shanghai: + 86 21 2412 1618/19 Sydney: +61 2 9751 8500



Our powerful portfolio of brands:

CADDY

**ERICO** 

**HOFFMAN** 

**ILSCO** 

**SCHROFF** 

**TRACHTE** 

©2025 nVent. All nVent marks and logos are owned or licensed by nVent Services GmbH or its affiliates. All other trademarks are the property of their respective owners. nVent reserves the right to change specifications without notice.