

# EDT2 Enhanced DIN Rail Surge Protection Class II, 4+0 Mode



## CERTIFICATIONS



## FEATURES

Includes nVent ERICO TD Technology to ensure reliability throughout adverse voltage conditions

Enhanced temporary over voltage (TOV) withstand capability

External back-up fuse is not required up to 315 A (IEC only)

Compact, yet high surge rated pluggable design, using minimum DIN rail width

Retaining clip ensures enhanced vibration and shock resistance performance

Red/Green status indication and change-over contacts standard for remote monitoring


## SPECIFICATIONS

Catalog Number	EDT248040R	EDT230040R
Nominal System Voltage (Un)	400 V	240 V
Max Continuous Operating Voltage (Uc)	480 V	300 V
Nominal Discharge Current (In), IEC	20kA 8/20 $\mu$ s	20kA 8/20 $\mu$ s
Max Discharge Current (Imax), IEC	50kA 8/20 $\mu$ s	50kA 8/20 $\mu$ s

Catalog Number	EDT248040R	EDT230040R
Voltage Protection Level (Up)	2300V	1650V
Back-Up Fuse @ Isccr	250 A @ 50 kA 315 A @ 25 kA	250 A @ 50 kA 315 A @ 25 kA
Frequency	50 - 60 Hz	50 - 60 Hz
Response Time	25 ns Max	25 ns Max
Protection Modes	L-PE N-PE	L-PE N-PE
Short Circuit Current Rating (Isccr)	25kA 50kA	25kA 50kA
Temporary Over Voltage 120 min (Ut/mode)	762 V Withstand	442 V Withstand
Nominal Discharge Current (In), UL	20kA 8/20 $\mu$ s	20kA 8/20 $\mu$ s
Short Circuit Current Rating (SCCR)	200kA	150kA
Voltage Protection Rating (VPR)	1800V	1200V
Technology	Thermal Disconnect	Thermal Disconnect
Connection, Solid	35 mm <sup>2</sup> Max	35 mm <sup>2</sup> Max
Connection, Stranded	25 mm <sup>2</sup> Max	25 mm <sup>2</sup> Max
Torque (TQ)	4.5 N·m	4.5 N·m
Humidity	5 - 95	5 - 95
Temperature	-35 to 85 °C	-35 to 85 °C
Enclosure Material	UL® 94V-0 Thermoplastic	UL® 94V-0 Thermoplastic
Enclosure Rating	IP 20	IP 20
Mounting	35 mm top hat DIN rail	35 mm top hat DIN rail
Remote Contact Switching Capacity	1 A @ 250 VAC 1 A @ 125 VAC 0.5 A @ 48 VDC 0.5 A @ 24 VDC 0.5 A @ 12 VDC	1 A @ 250 VAC 1 A @ 125 VAC 0.5 A @ 48 VDC 0.5 A @ 24 VDC 0.5 A @ 12 VDC
Remote Contacts	Yes	Yes
Status Indication	Mechanical flag	Mechanical flag
Depth (D)	69mm	69mm
Height (H)	90 mm	90 mm
Width (W)	72 mm	72 mm
Unit Weight	0.56 kg	0.52 kg
Certification Details	UL® 1449 Edition 5 Type 1CA	UL® 1449 Edition 5 Type 1CA
Complies With	EN 61643-11 Type 2 IEC® 61643-11 Class II	EN 61643-11 Type 2 IEC® 61643-11 Class II

<b>Catalog Number</b>	<b>EDT248040R</b>	<b>EDT230040R</b>
Replacement Module	EDT2480M	EDT2300M

## DIAGRAMS



## WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at [www.nvent.com](http://www.nvent.com) and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.

### North America

+1.800.753.9221  
Option 1 – Customer Care  
Option 2 – Technical  
Support

### Europe

Netherlands:  
+31 800-0200135  
France:  
+33 800 901 793

### Europe

Germany:  
800 1890272  
Other Countries:  
+31 13 5835404

### APAC

Shanghai:  
+ 86 21 2412 1618/19  
Sydney:  
+61 2 9751 8500



Our powerful portfolio of brands:

**CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE**