

# ProLine Disconnect Doors



Disconnect Doors provide a means to mount flange-mount disconnects to ProLine Enclosures. Hinged mullion provides unobstructed access to interior, thus easing equipment installation.

Disconnect mullion is hinged to provide easy disconnect installation and maximum access to subpanel. Removable door bar is included on disconnect door. A flush handle with defeater operates an internal 3-point latch system on disconnect door and latches to the disconnect mullion. Interlocking is provided from Primary door to disconnect mullion. The disconnect mullion and disconnect door include 140-degree hinges and are gasketed to maintain enclosure integrity.

## FEATURES

Includes a flush handle with defeater and 3-point latching system

Enclosures with a preferred cutout will accept the disconnect switches listed in the Preferred Cutout Overview section.

Enclosures with a large cutout will accept the disconnect switches listed in the Large Cutout Overview section.

## SPECIFICATIONS

**Thickness:** 1.9mm  
**Color:** Light Gray  
**Finish:** Powder Coated  
**Color Code:** RAL 7035

Table 1/1

| Catalog Number | Article Number | Material   | Dimensions    | Cutout Type          | Fits Frame    | Quick Ship |
|----------------|----------------|------------|---------------|----------------------|---------------|------------|
| PLTDDC166      | 35639          | Mild Steel | 1539 x 594mm  | Preferred left-hand  | 1600 x 600mm  | No         |
| PTDDC166       | 35629          | Mild Steel | 1539 x 594mm  | Preferred right-hand | 1600 x 600mm  | No         |
| PLTDDC168      | 22939          | Mild Steel | 1539 x 794mm  | Preferred left-hand  | 1600 x 800mm  | No         |
| PTDDC168       | 36570          | Mild Steel | 1539 x 794mm  | Preferred right-hand | 1600 x 800mm  | No         |
| PLTDDC1810     | 22969          | Mild Steel | 1739 x 994mm  | Preferred left-hand  | 1800 x 1000mm | No         |
| PTDDC1810      | 36940          | Mild Steel | 1739 x 994mm  | Preferred right-hand | 1800 x 1000mm | No         |
| PTDDC186       | 35649          | Mild Steel | 1739 x 594mm  | Preferred right-hand | 1800 x 600mm  | No         |
| PLTDDC188      | 22949          | Mild Steel | 1739 x 794mm  | Preferred left-hand  | 1800 x 800mm  | No         |
| PTDDC188       | 36580          | Mild Steel | 1739 x 794mm  | Preferred right-hand | 1800 x 800mm  | No         |
| PTDLDC2010     | 22679          | Mild Steel | 2000 x 1000mm | Large right-hand     | 2000 x 1000mm | No         |
| PTDDC2010      | 36950          | Mild Steel | 1939 x 994mm  | Preferred right-hand | 2000 x 1000mm | No         |
| PLTDDC2010     | 22979          | Mild Steel | 1939 x 994mm  | Preferred left-hand  | 2000 x 1000mm | No         |
| PTDLDC206      | 35709          | Mild Steel | 1939 x 594mm  | Large right-hand     | 2000 x 600mm  | No         |
| PTDDC206       | 35669          | Mild Steel | 1939 x 594mm  | Preferred right-hand | 2000 x 600mm  | No         |
| PLTDDC208      | 22959          | Mild Steel | 1939 x 794mm  | Preferred left-hand  | 2000 x 800mm  | No         |
| PTDDC208       | 36590          | Mild Steel | 1939 x 794mm  | Preferred right-hand | 2000 x 800mm  | No         |

## ADDITIONAL PRODUCT DETAILS

---

Allen-Bradley: Large handle to be used with 400A or greater disconnect switches and 600A or greater circuit breakers.

Siemens ITE: MAX-FLEX™ FHOHN handle used with MD 800 amp, ND (1200 amp), PD (1600 amp) and RD (2000 amp).

## WARNING

---

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at [www.nvent.com](http://www.nvent.com) and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.



Our powerful portfolio of brands:

**CADDY   ERICO   HOFFMAN   ILSCO   SCHROFF   TRACHTE**