nVent HOFFMAN

We connect and protect

# Thermoelectric Cooler TE16 24V with Shroud, 15.93x7.35x7.27, Brushed, SS304

## CATALOG NUMBER

**TE162024011**

Thermoelectric Coolers minimize downtime and component loss by removing heat around critical components within an enclosure. These compact, low-profile coolers using the Peltier effect allow for cooling of small indoor and outdoor enclosures. No condensers, compressors or filters are required making it a reliable solution for demanding low-maintenance environments and low noise.

Operates on the Peltier effect for cooling or heating

## INDUSTRY STANDARDS

UR, cUR Recognized; Type 12, 3R, 4, 4X; File No. SA6453

CE

IP 65

## FEATURES

- Operates on the Peltier effect for cooling or heating
- Contains no refrigerant, making it earth friendly
- Filterless design reduces maintenance requirements
- Compressor-free air conditioning for demanding indoor and outdoor applications
- Prewired with simple terminal block for easy wiring connections
- Shrouded and unshrouded models included in standard packages
- Operating temperature range -40 C (-40 F) to 55 C (131 F)
- Partial recess mount
- DC Powered operation for 24V and 48V applications
- Low profile design allows for mounting vertically and horizontally on any enclosure to avoid interference with internal components

## PRODUCT ATTRIBUTES

- Article Number: 21067
- Height: 405mm
- Width: 187mm

Depth: 185mm

Nominal Voltage: 24V

Nominal Capacity Btu/h: 567Btu/h

Nominal Capacity Watts: 166W

Voltage DC: 18V

Max Current: 14.7A

Operating Temperature: −40 to 55°C

Material: Stainless Steel 304

Finish: Brushed #4

Thickness: 1.52mm

## WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.



©2025 nVent. All nVent marks and logos are owned or licensed by nVent Services GmbH or its affiliates. All other trademarks are the property of their respective owners. nVent reserves the right to change specifications without notice.

This document is system-generated.