

Adjustable I-Beam Adapter



This code-compliant Structural Attachment is part of the nVent CADDY line of innovative rigid bracing system, designed to provide superior performance and meet the highest seismic load requirements. Its innovative design allows quick and easy installation onto a wide range of steel I-Beams. It is ready to use out of the box, eliminating the need for pre-assembly or loose hardware and its snap-off bolts make inspection of seismic sway braces simple.

FEATURES

No loose parts

No assembly required

Snap-off bolt head helps enable easy installation and inspection of seismic sway braces

Meets NFPA®-13 requirements for seismic sway bracing

FM® Specification Tested

SPECIFICATIONS

Material: Steel

Table 1/2							
Catalog Number	Finish	Flange Thickness (FT)	A	Rod Size 1 (RS1)	Rod Size 2 (RS2)	Height (H)	
CSBS3HDN	Hot-Dip Galvanized	6 - 19 mm	100 - 215 mm	3/8"	1/2"	67 mm	
CSBS4N	Electrogalvaniz ed	6 - 19 mm	100 - 365 mm	3/8"	1/2"	67 mm	
CSBS4HDN	Hot-Dip Galvanized	6 - 19 mm	100 - 365 mm	3/8"	1/2"	67 mm	
CSBS3N	Electrogalvaniz ed	6 - 19 mm	100 - 215 mm	3/8"	1/2"	67 mm	
CSBS5HDN	Hot-Dip Galvanized	19 - 31 mm	100 - 455 mm	3/8"	1/2"	79 mm	

CatalogNumber	Finish	Flange Thickness (FT)	A	Rod Size 1 (RS1)	Rod Size 2 (RS2)	Height (H)
CSBS5N	Electrogalvaniz ed	19 - 31 mm	100 - 455 mm	3/8"	1/2"	79 mm

Table 2/2						
Catalog Number	Width (W)					
CSBS3HDN	92 mm					
CSBS4N	92 mm					
CSBS4HDN	92 mm					
CSBS3N	92 mm					
CSBS5HDN	92 mm					
CSBS5N	92 mm					


ADDITIONAL PRODUCT DETAILS

Structure Attachment and Brace Member are not included.

UL Loads						
Part Number	Structure Attachment Fitting	Flange Thickness	Brace Member	Load Rating		
CSBS3xxx	CCDU1	6 - 8 mm	DN25 - DN50 Sch. 40 NPS	6672 N		
	CSBU1xxx	8 - 19 mm	DIN25 - DIN50 SCII. 40 NPS	7561 N		
			CSB12CBL	1859 N		
	CSBURC12	6 - 19 mm	CSB18CBL	3434 N		
			CSB36CBL	4893 N		
CSBS4xxx	000111	6 - 8 mm	DNIGE DNIEGO-L 40 NIPO	6672 N		
	CSBU1xxx	8 - 19 mm	DN25 - DN50 Sch. 40 NPS	7561 N		
			CSB12CBL	1859 N		
	CSBURC12	6 - 19 mm	CSB18CBL	3434 N		
			CSB36CBL	4893 N		
CSBS5xxx	CSBU1xxx	6 - 19 mm	DN25 - DN50 Sch. 40 NPS	7561 N		
			CSB12CBL	1859 N		
	CSBURC12	6 - 19 mm	CSB18CBL	3434 N		
			CSB36CBL	4893 N		

FM Loads									
Part Number	Horizontal Ca	Horizontal Capacity per Installation Angle from Vertical							
	Perpendicula	Perpendicular to Structure			Parallel to S	Parallel to Structure			
	30°- 44°	45°- 59°	60°- 74°	75°- 90°	30°- 44°	45°- 59°	60°- 74°	75°- 90°	
CSBS3xxx	5240 N	9830 N	12580 N	13070 N	3640 N	6130 N	9250 N	13380 N	
CSBS4xxx	5240 N	9830 N	12580 N	13070 N	3640 N	6130 N	9250 N	13380 N	
CSBS5xxx	5420 N	9510 N	11470 N	12760 N	4890 N	8090 N	9740 N	11920 N	

DIAGRAMS



WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.

North America

+1.800.753.9221 Option 1 – Customer Care Option 2 – Technical Support

Europe

Netherlands: +31 800-0200135 France: +33 800 901 793

Europe

Germany: 800 1890272 Other Countries: +31 13 5835404

APAC

Shanghai: + 86 21 2412 1618/19 Sydney: +61 2 9751 8500



Our powerful portfolio of brands:

CADDY

ERICO

HOFFMAN

ILSCO

SCHROFF

TRACHTE

©2025 nVent. All nVent marks and logos are owned or licensed by nVent Services GmbH or its affiliates. All other trademarks are the property of their respective owners. nVent reserves the right to change specifications without notice.