We connect and protect

Connector Type H, EN 60603, DIN 41612, Female, 15 Contacts, FASTON 6.3 mm

CATALOG NUMBER

69001-733





Male / Female DIN connector form H. Requirement class 2 as per EN 60603 (DIN 41642).

CERTIFICATIONS

FEATURES

- Requirement class 2 as per EN 60603 (DIN 41642)
- Separate Coding
- Coding on the connector

PRODUCT ATTRIBUTES

Type: Female Connectors

Package Quantity: 1

Number of Contacts: 15

Contact Material: Silver Plated

Connector Pitch: 5.08mm

Min Creepage Distance, Contact-Contact: 8mm

Min Air Gap, Contact-Contact: 4.5mm

Max Current @ 20°C: 6A

Max Contact Resistance: 8mO

Max Insertion and Withdrawal Force: 90N

Test Voltage (Ueff), Contact-Contact: 1.55kV

Test Voltage (Ueff), Contact-Earth: 2.5kV

Row Assignment: Z; D

Finish: Silver Plated

Product Type: Connector

Works With: Front Panels

Connection Type: Faston, 6.3 mm

WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.

North America
All locations
+1.763.422.2661
Chat with us:
nvent.com/schroff

Europe
Straubenhardt, Germany
+49.7082.794.0
Betschdorf, France
+33.3.88.90.64.90
Warsaw, Poland
+48.22.209.98.35
Assago, Italy
+39.02.932.7141
Chat with us:
nvent.com/schroff

Asia
Shanghai, China
+86.21.2412.6943
Qingdao, China
+86.532.8771.6101
Singapore
+65.6768.5800
Shin-Yokohama, Japan
+81.45.476.0271
Chat with us:
nvent.com/schroff

Middle East & India
Dubai, United Arab Emirates
+971.4.378.1700
Bangalore, India
+91.80.6715.2001
Istanbul, Turkey
+90.216.250.7374
Chat with us:
nvent.com/schroff

Our powerful portfolio of brands:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE

©2025 nVent. All nVent marks and logos are owned or licensed by nVent Services GmbH or its affiliates. All other trademarks are the property of their respective owners. nVent reserves the right to change specifications without notice.

This document is system-generated.