




**PYROTENAX**

# System 2000 MI Wiring Alloy 825 Cable



nVent PYROTENAX System 2000 mineral insulated (MI) wiring cable is a range of MI wiring cable, with an Alloy 825 sheath and nickel-clad copper conductors (600 V). It has a continuous exposure temperature of 1238 °F/670 °C and can withstand rapid-rise temperature excursions to 2000 °F/1093 °C. The inorganic cable construction provides superior fire resistance under conditions of both high heat flux and high temperature. Common applications include the supply of power to motor operated valves during fire exposure ensuring that valves can be safely controlled and closed when required. It is typically supplied as a factory-assembled wiring unit complete with terminations at each end.

## FEATURES

Ultimate performance: zero smoke generation, zero fuel contribution and zero flame spread.; no flow or transmission of explosive gases through the wiring cables

Maintains electrical circuit integrity for 30 minutes in the UL 1709 fire test, using UL2196 test procedure (UL 1709 test, referenced in API 2218, replicates an intense hydrocarbon fire, reaching 2000 °F/1093 °C in 5 minutes when subjected to a heat flux of 65,000 BTU/ft<sup>2</sup> hr (200 kW/m<sup>2</sup>) in an enclosed furnace).

Reliable during long life: 30 year product warranty available

Approved for hazardous locations

## SPECIFICATIONS

<b>Voltage Rating:</b>	600 V
<b>Max Operating Temperature:</b>	670 °C
<b>Max Exposure Temperature:</b>	1093 °C
<b>Sheath Material:</b>	Alloy 825
<b>Flame Retardant:</b>	In Accordance with EN 60332-3-24
<b>Insulation Material:</b>	Magnesium Oxide
<b>Construction:</b>	Mineral Insulated Cable
<b>Conductor Material:</b>	Nickel Clad Copper

Table 1/2

Catalog Number	Item Name	Core Quantity	Current Rating @ 70°C	Current Rating @ 75°C	Current Rating @ 90°C	Outer Diameter
----------------	-----------	---------------	-----------------------	-----------------------	-----------------------	----------------

215/1NC1.0/825		1	22 A			5.5 mm
240/1NC1.5/825		1	27 A			6.1 mm
253/1NC2.5/825		1	36 A			6.4 mm
286/1NC4.0/825		1	47 A			7.3 mm
527/1NC35.0/825		1	168 A			13.4 mm
480/1NC25.0/825		1	139 A			12.2 mm
480-3/1NC825	1C/3AWG/SYS 2000 600V	1		145 A	165 A	12.2 mm
340/1NC6.0/825		1	59 A			8.6 mm
434-4/1NC825	1C/4AWG/SYS 2000 600V	1		125 A	140 A	11 mm
402/3NC1.0/825		3	15 A			10.2 mm
402/2NC1.5/825		2	23 A			10.2 mm
387/1NC10.0/825		1	81 A			9.8 mm
434/1NC16.0/825		1	107 A			11 mm
465/3NC1.5/825		3	20 A			11.8 mm

480/3NC2.5/82 5		3	27 A			12.2 mm
496/2NC4.0/82 5		2	42 A			12.6 mm
496/7NC1.0/82 5		7	15 A			12.6 mm
684/2NC10.0/8 25		2	74 A			17.4 mm
714/3NC10.0/8 25		3	62 A			18.1 mm
543/2NC6.0/82 5		2	54 A			13.8 mm
543/7NC1.5/82 5		7	20 A			13.8 mm
590/3NC6.0/82 5		3	46 A			15 mm
590/4NC4.0/82 5		4	36 A			15 mm
714/7NC4.0/82 5		7	36 A			18.1 mm
750/7NC6.0/82 5		7	46 A			19.1 mm

Table 2/2

Catalog Number	Item Name	AWG Size	Conductor Cross-Section
215/1NC1.0/825			1 mm <sup>2</sup>
240/1NC1.5/825			1.5 mm <sup>2</sup>
253/1NC2.5/825			2.5 mm <sup>2</sup>

Catalog Number	Item Name	AWG Size	Conductor Cross-Section
286/1NC4.0/825			4 mm <sup>2</sup>
527/1NC35.0/825			35 mm <sup>2</sup>
480/1NC25.0/825			25 mm <sup>2</sup>
480-3/1NC825	1C/3AWG/SYS 2000 600V	#3	
340/1NC6.0/825			6 mm <sup>2</sup>
434-4/1NC825	1C/4AWG/SYS 2000 600V	#4	
402/3NC1.0/825			1 mm <sup>2</sup>
402/2NC1.5/825			1.5 mm <sup>2</sup>
387/1NC10.0/825			10 mm <sup>2</sup>
434/1NC16.0/825			16 mm <sup>2</sup>
465/3NC1.5/825			1.5 mm <sup>2</sup>
480/3NC2.5/825			2.5 mm <sup>2</sup>
496/2NC4.0/825			4 mm <sup>2</sup>
496/7NC1.0/825			1 mm <sup>2</sup>
684/2NC10.0/825			10 mm <sup>2</sup>
714/3NC10.0/825			10 mm <sup>2</sup>
543/2NC6.0/825			6 mm <sup>2</sup>
543/7NC1.5/825			1.5 mm <sup>2</sup>

Catalog Number	Item Name	AWG Size	Conductor Cross-Section
590/3NC6.0/825			6 mm <sup>2</sup>
590/4NC4.0/825			4 mm <sup>2</sup>
714/7NC4.0/825			4 mm <sup>2</sup>
750/7NC6.0/825			6 mm <sup>2</sup>

## WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at [www.nvent.com](http://www.nvent.com) and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.

### North America

Tel +1.800.545.6258  
 Fax +1.800.527.5703  
[thermal.info@nvent.com](mailto:thermal.info@nvent.com)

### Europe, Middle East, Africa

Tel +32.16.213.511  
 Fax +32.16.213.604  
[thermal.info@nvent.com](mailto:thermal.info@nvent.com)

### Asia Pacific

Tel +86.21.2412.1688  
 Fax +86.21.5426.3167  
[cn.thermal.info@nvent.com](mailto:cn.thermal.info@nvent.com)

### Latin America

Tel +1.713.868.4800  
 Fax +1.713.868.2333  
[thermal.info@nvent.com](mailto:thermal.info@nvent.com)

Our powerful portfolio of brands:

**RAYCHEM PYROTENAX TRACER NUHEAT**